## **Data Sheet**

# Within Series Adaptor 34\_N-75-0-1/133\_N



#### **Description**

Bulkhead adaptor jack/jack N jack (female) / N jack (female)

Interface standard
Series N - Not compatible to N 50 Ohms



#### **Technical Data**

**Electrical Data** 

 $\begin{array}{ll} \text{Impedance} & 75 \, \Omega \\ \text{Interface frequency max.} & 1.5 \, \text{GHz} \end{array}$ 

**Mechanical Data** 

Number of matings 500
Weight 0.0464 kg

**Environmental Data** 

Operating temperature -65 °C to 165 °C 2011/65/EU (RoHS) compliant

**Material Data** 

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	

#### Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	

#### **Related Documents**

Catalogue drawing DCA-00013619

### **Ordering Information**

Single package 34\_N-75-0-1/133\_NE

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.