

ELECTRONICS PLIERS


Electronics Pliers

35

- > precision pliers for fine assembly work,
 e g. in electronics and fine mechanics
- > for gripping, holding and bending
- > sturdy, zero backlash box joint
- > smooth ground gripping surfaces
- > edges carefully deburred
- > low-friction double spring for gentle and even opening
- > the polish or mirror polish (only finish 2) together with a fine film of oil offer effective rust protection – no circuit faults caused by peeling chrome from plated tools
- > Special tool steel, forged, oil-hardened












35 32 115 8 <☐ ☐ MM











^{35 82 145} ⊗ ∠45° ⊖ ⊂ ⊂ ∞ ∞ ∞

						Dimensions					
	EAN	∢ →				В	А	D	Е	F	52
Article No.	4003773-	mm		Head	Handles	mm	mm	mm	mm	mm	g
35 11 115	016694	115		mirror polished	plastic coated	22.5	9.5	6.5	2.0	4.0	61
35 12 115	035107	115	*=	mirror polished	with multi-component grips	22.5	9.5	6.5	2.0	4.0	72
35 21 115	016724	115	₩⊖⊂]⊑/MM	mirror polished	plastic coated	22.5	9.5	6.5	2.0	1.5	59
35 22 115	035114	115	₩⊖⊂]⊑/MM	mirror polished	with multi-component grips	22.5	9.5	6.5	2.0	1.5	73
35 31 115	016762	115	₩8⊂]⊑JMM	mirror polished	plastic coated	22.5	9.5	6.5	2.0	1.0	58
35 32 115	035121	115	₩8⊂]⊑JMM	mirror polished	with multi-component grips	22.5	9.5	6.5	2.0	1.0	72
35 42 115	040736	115	\$\$≰45°⊖⊂]⊡MM	mirror polished	with multi-component grips	22.5	9.5	6.5	2.0	1.5	74
35 52 145	039389	145	*=M	mirror polished	with multi-component grips	40.0	12.0	7.5	1.5	4.0	102
35 62 145	039556	145	₩0⊂]⊑JMM	mirror polished	with multi-component grips	40.0	12.0	7.5	2.5	1.5	103
35 72 145	043607	145	₩8⊂]⊑JMM	mirror polished	with multi-component grips	40.0	12.0	7.5	2.5	1.3	98
35 82 145	039396	145	\$\$≴45°⊖⊂]⊡™M	mirror polished	with multi-component grips	35.0	12.0	7.5	2.5	1.0	102