



Datasheet

Stock No: 362-6712

Straight Male 1in Part C Cam & Groove Coupler, Aluminium



Product Details

Part C Coupler

Cam female x hose tail

Aluminium coupling with stainless steel pins and brass handles

Cam & Groove Couplings - Aluminium

Conform to MIL-C-27487

Buna-N sealing ring

Working pressure 17 bar (250psi)

Seal temperature range -40°C to +80°C

Specifications:

Hose Inner Diameter	1in
Coupling Connector Type	Part C Cam & Groove Coupler
Body Material	Aluminium
Thread Size	1in
Coupling Gender	Male
Coupling Connector Direction	Straight
Maximum Working Pressure	17 bar