

Product Datasheet

Product code: **363**

Product type: High Precision Scissors

Made in: Italy

Description: The 363 are high precision scissors with extra fine blades, ideal for miniature work. The rounded tip shape prevents accidental damages to the material. The curved blades prevent the tips from getting stuck in the material. The Inox material is suitable for cleaning. The blades are hardened to 55HRC hardness.

Tip description: curved, round

Coating/finishing: Sandblasted

Body material: Stainless Steel (Hardened AISI 420)

Picture:



Product dimensions:

OAL	90.0 mm – 3.543 inch
Width	45.0 mm – 1.772 inch
Height	5.0 mm – 0.197 inch

Tip dimensions:

Tip width	0.50 mm – 0.020 inch
Tip thickness	0.30 mm – 0.012 inch