

Product Datasheet

Product code: **364**

Product type: High Precision Scissors

Made in: Italy

Description: The 364 are high precision scissors with extra fine blades, ideal for strong work. The double tip allows to access small areas while the shape supports the cut. The curved blades prevent the tips from getting stuck in the material. The Inox material is suitable for cleaning. The blades are hardened to 55HRC hardness.

Tip description: curved, extra fine

Coating/finishing: Sandblasted

Body material: Stainless Steel (Hardened AISI 420)

Picture:



Product dimensions:

OAL	90.0 mm – 3.543 inch
Width	47.0 mm – 1.850 inch
Height	5.0 mm – 0.197 inch

Tip dimensions:

Tip width	0.50 mm – 0.020 inch
Tip thickness	0.40 mm – 0.016 inch