

Product Datasheet

Product code: 365

Product type: High Precision Scissors

Made in: Italy

Description: The 365 are high precision scissors with curved tips, ideal for delicate work. The curved blades prevent the tips from getting stuck in the material. The Inox material is suitable for cleaning. The blades are hardened to 55HRC hardness.

Tip description: curved, round

Coating/finishing: Sandblasted

Body material: Stainless Steel (Hardened AISI 420)

Picture:



Product dimensions:

OAL	90.0 mm – 3.543 inch
Width	45.0 mm – 1.772 inch
Height	5.0 mm – 0.197 inch

Tip dimensions:

Tip width	1.30 mm – 0.051 inch
Tip thickness	0.60 mm – 0.024 inch