



ENGLISH

SPECIFICATION SHEET

RS Stock No 365543

SOFT TINNED COPPER WIRE BRAID 2534P

CONSTRUCTION :	24x10x0.20MM
RESISTANCE :	2.3 OHMS/KM STANDARD RESISTANCE @ 20 DEG C.
YIELD :	80.4KGS/1000M
TENSILE :	N/A
WIRE :	MANUFACTURED TO BSEN 13602: 2002
RoHS :	COMPLIANT