()ideal-tek

Product Datasheet

Product code:	365
Product type:	Scissors
Made in:	Italy
Description:	The 365 are high precision scissors. The curved blades prevent the tips from getting stuck in the material. The curved tips are ideal for delicate work. The Inox material is suitable for cleaning. The blades are hardened to 55HRC hardness.
Tip description:	round tips, curved blade
Body material:	Inox
Picture:	

Product dimensions:

OAL Width Height 90.0 mm – 3.543 inch 45.0 mm – 1.772 inch 5.0 mm – 0.197 inch