

SOLID ABS 3828 18 G



Sample photo

Order symbol: ABS 3828 18 G
Product nbr: 5880373
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074039095
EI. number:
 Finland: 3423769
 Electric No. Italy: 7410155
 Electric No. Sweden: 2539723

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	378	278	180	EKPXT	Mounting plate isolated
inch:	14.9	10.9	7.1	EKV 22	DIN-35 Mounting rail
Materials:				EKV 32	DIN-35 Mounting rail
Material:	ABS			EKPZR	Extension frame
Base colour:	RAL 7035 -light grey			Rating:	
Cover screws material:	Polyamide			Ingress Protection (EN 60529): IP66/IP67	
Cover colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK08	
Cover screws colour:	Grey			Electrical insulation: Totally insulated	
Gasket material:	Polyurethane			Halogen free (DIN/VDE 0472, Part 815): 1	
Temperatures:				Flammability Rating: UL 94 HB	
Temperature °C (short term):	-40 ... 80 °C			Glow Wire Test (IEC 695-2-1) °C: 650	
Temperature °C (continuous):	-40 ... 60 °C			NEMA Class: NEMA 1, 4, 4X, 6, 12, 13	
Temperature °F (short term):	-40 ... 175 °F			Certificates:	
Temperature °F (continuous):	-40 ... 140 °F			SGS Fimko	
Accessories:					
EKPV1	Mounting plate				

