

**SOLID PC 3828 18 T**



Sample photo

**Order symbol:** PC 3828 18 T  
**Product nbr:** 5330073  
**Description:** Enclosure, PC  
**Remarks:** Transparent cover

**EAN:** 6418074005571  
**EI. number:**  
 Finland: 3423819  
 Electric No. Italy: 7402055  
 Electric No. Sweden: 2539454

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	378	278	180	EKPXT	Mounting plate isolated
inch:	14.9	10.9	7.1	EKV 22	DIN-35 Mounting rail
				EKV 32	DIN-35 Mounting rail
				EKPZR	Extension frame
Materials:				Rating:	
<b>Material:</b>	Polycarbonate			Ingress Protection (EN 60529): IP66/IP67	
<b>Base colour:</b>	RAL 7035 -light grey			Impact Resistance (EN 62262): IK08/IK09	
<b>Cover screws material:</b>	Polyamide			Electrical insulation: Totally insulated	
<b>Cover colour:</b>	Clear transparent			Halogen free (DIN/VDE 0472, Part 815): 1	
<b>Cover screws colour:</b>	Grey			UV resistance: UL 508	
<b>Gasket material:</b>	Polyurethane			Flammability Rating: UL 746C 5"	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12	
Temperatures:				Certificates:	
<b>Temperature °C (short term):</b>	-40 ... 120 °C			SGS Fimko	
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			Gost R	
<b>Temperature °F (short term):</b>	-40 ... 250 °F				
<b>Temperature °F (continuous):</b>	-40 ... 175 °F				
Accessories:					
EKPVT	Mounting plate				

