

## Datasheet

# RS Pro 2 Way Earth Block, Screw Down 16 to 6 AWG, 54mm length, Green/Yellow

RS Stock No: **384-7010**



## Product Details

RS Pro spring clamp terminal block accept industry standard 5 x 20 mm glass cartridge fuses. This fuse terminal block has a built in end plate leaving no live part exposed. The CXF terminal block can be internally bridged using standard shorting accessories. The spring terminal block is very easy to use and saving nearly 80% of wiring time compared to screw connections. These fuse terminal block is used in electrical and control systems which require fuse protection.

## Features and Benefits

- Compact design
- Low contact resistance
- Corrosion proof terminal points
- Large surface labelling
- Vibration resistant and gas tight connections

**Specifications:**

Cable CSA	10 mm <sup>2</sup>
Colour	Green/Yellow
Current Rating	57 A
Height	62.5 mm
Housing Material	Nylon
Length	54 mm
Number of Ways	2
Termination Method	Screw Down
Voltage Rating	800 V
Width	10 mm
Wire Size	16 to 6 AWG