



39 - METRIC SHORT-REACH COMBINATION WRENCHES | 39.13





Description

- Short combination wrenches: the short handle and compact head allow for high handiness. Ideal for confined access.
- OGV® profile with 12-point ring for powerful tightening while protecting the nut. H suffix = 6-point ring.
- Ring head angled at 15°.
- Open end head angled at 15°.
- Metric sizes: 3.2 to 17 mm.
- Presentation: satin chrome finish.

Information

A [mm]	13
E [mm]	5,8
L [mm]	141
[9]	55

© FACOM 2018