

FEATURES

- Easy to fit to rack or cabinet
- Mounting plate 25 x 35 mm in Yellow ABS - easily recognised marking yellow on black colours
- Complete with isolated screw for earth connection
- 1 x 10 mm male stud connection

RS PRO ESD Rack Bonding Point with 10 mm Stud

RS Stock No.: 392-141



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO anti-static easy to fit rack bonding point lets you create a designated ESD grounding point on panels, racks and cabinets. The EBP kit has a 10 m connection which is then electrically bonded to the mounting or earth by the user. The mounting plate is 25 x 35 mm in size and clearly states 'ESD BONDING POINT'..

10mm Press Stud
 M5 Ring Terminal
 Vinyl Plate
 M3 Nut
 Plastic Shoulder Washer
 M3 Screw
 Shaker proof Washer
 M3 Washer

General Specifications

Accessory Type	Rack Bonding Points
Connector Type	10 mm Stud
Complies with EN 61340-5-1	Yes
Includes Cord	Yes
Colour	Yellow
Application	ESD grounding accessories form part of a workplace safety system to monitor and/or eliminate the build-up or discharge of static electricity that may pose a risk to electrical components such as computer hard drives

Mechanical Specifications

Stud Size	10mm
Dimensions	25mm x 35mm

Approvals

Compliance/Certifications	ESD S20.20 and EN 61340-5-1 ESD , IEC 61340-5-2 V
----------------------------------	---



Dimensions

