



SENTRON, cylindrical fuse holder, 10x38 mm, 3-pole, In: 32 A, Un AC: 690 V

Model	
product brand name	SENTRON
product designation	Cylindrical fuse holder
General technical data	
number of poles	3
size of fuse link	10 x 38 mm
Supply voltage	
operating voltage	690 V
• at AC / rated value	
protection class IP	IP20
Current	
operational current / at AC / rated value	32 A
Mechanical Design	
height	81 mm
width	54 mm
depth	64 mm
net weight	185 g
Certificates	
reference code	F
• acc. to DIN EN 61346-2	
• acc. to IEC 81346-2	F
General Product Approval	Declaration of Conformity



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW7033>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NW7033>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7033

Tender specifications



