## **SIEMENS**

Data sheet 3VA9988-0AA12

AUXILIARY SWITCH CHANGEOVER CONTACTS TYPE HQ (7MM) ACCESSORY FOR 3VA1 and 3VA20 up to 3VA25



Model				
Product brand name	SENTRON			
Product designation	auxiliary switch			
Product version	Accessories for 3VA circuit breakers			
Accessories	Auxiliary switch			
General technical data				
Degree of pollution	3			
Overvoltage category	III			
Voltage				
Rated insulation voltage Ui	690 V			
Rated impulse withstand voltage	4 kV			
Rated operational voltage Ue at AC 50 Hz	240 V			
Rated operational voltage Ue with DC	250 V			
Electricity				
Thermal current limit Ith	6 A			
Operating current				
• at AC-12 / at 12 V	6 A			
• at AC-12 / at 24 V	6 A			

• at AC-12 / at 48 V	6 A
• at AC-12 / at 110 V	6 A
• at AC-12 / at 230 V	6 A
• at DC-12 / at 12 V	6 A
• at DC-12 / at 24 V	4 A
• at DC-12 / at 48 V	2 A
• at DC-12 / at 110 V	0.5 A
• at DC-12 / at 230 V	0.25 A
• at DC-13 / at 12 V	1 A
• at DC-13 / at 24 V	0.8 A
• at DC-13 / at 48 V	0.4 A
• at DC-13 / at 110 V	0.2 A
• at DC-13 / at 220 V	0.1 A
• at AC-15 / at 12 V	3 A
• at AC-15 / at 24 V	3 A
• at AC-15 / at 48 V	3 A
• at AC-15 / at 110 V	3 A
• at AC-15 / at 230 V	3 A

Mechanical Design	
Height	56 mm
Width	7 mm
Width / Note	1 slot (7 mm)
Depth	30 mm
Net weight	30 g
Tightening torque / with screw-type terminals / minimum	0.4 N·m
Tightening torque / with screw-type terminals / maximum	0.5 N·m

Connections according IEC		
Wire stripping length	15 mm	
AWG number / as coded connectable conductor cross section / for auxiliary contacts		
• minimum	20	
• maximum	16	

Connetctions according UL	
Wire stripping length [in]	0.6 in
Tightening torque [lbf·in] / with screw-type terminals / minimum	3.5 lbf·in
Tightening torque [lbf·in] / with screw-type terminals / maximum	4.4 lbf·in

## Certificates

## **General Product Approval**

**EMC** 

Declaration of Conformity





Miscellaneous







Test Certific- ates	Shipping Ap- proval	other		
Type Test Certificates/Test Report	Lloyd's Register	Manufacturer De- claration	Miscellaneous	
	LRS			

## **Further information**

Information- and Downloadcenter (Catalogs, Brochures,...)

http://www.siemens.com/lowvoltage/catalogs

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9988-0AA12

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3VA9988-0AA12

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax\_en.aspx?mlfb=3VA9988-0AA12


**CAx-Online-Generator** 


http://www.siemens.com/cax

Tender specifications

http://www.siemens.com/specifications







**last modified:** 02/28/2019