SIEMENS

Product data sheet 3RT2926-1ER00



SURGE SUPPRESSOR, DIODE COMBINATION, DC 24 V, FOR MOTOR CONTACTORS SZ S0,

General technical data:				
product brand name		SIRIUS		
product designation		surge suppressor		
Size of the contactor		S0		
Design of the surge suppressor		with diode assemblies		
Ambient temperature				
during storage	°C	-40 +80		
during operating	°C	-25 +60		

Control circuit:				
Type of voltage / of the controlled supply voltage		DC		
Control supply voltage frequency				
• 1 / rated value	Hz	0		
Control supply voltage / 1				
• for DC				
• rated value	V	24		

Installation/mounting/dimensions:				
Built in orientation		any		
Type of mounting		clip-on		
Width	mm	30		

Height	mm	19
Depth	mm	12

Certificates/approvals:

Verification of suitability CE / UL / CSA / CCC

General Product Approval

Test Certificates



ROSTEST



Manufacturer

Shipping Approval













Shipping Approval

other



Manufacturer



Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

http://www.siemens.com/industrial-controls/catalogs

Industry Mall (Online ordering system)

http://www.siemens.com/industrial-controls/mall

CAx-Online-Generator


http://www.siemens.com/cax


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

http://support.automation.siemens.com/WW/view/en/3RT2926-1ER00/all

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

 $\underline{\text{http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3RT2926-1ER00}$





¥ |

last change: Feb 6, 2012