## SIEMENS

## Product data sheet


## 3SE7120-1BF00


SIRIUS CABLE-OPER. SWITCH METAL HOUSING,2X M20X1.5 2NC, LATCHES ACC. EN ISO 13850 BUTTON RESET FOR CABLES UP TO TO 10M



General technical details:					
product designation		cable-operated switch			
Number of indicator lights		0			
Type of unlocking device		push-to-unlatch mechanism			
Rope length / maximum	m	10			
Product component / EMERGENCY STOP device		Yes			
Item designation / according to DIN 40719 extendable after IEC 204-2 / according to IEC 750		S			
Item designation / according to DIN EN 61346-2		S			
Width	mm	52			
Height	mm	164.5			
Depth	mm	57.5			
Enclosure:					
Type of mounting		screw fixing			
material / of the housing		metal			
Color / of the top part of housing		grey			
Contact:					
Number of NC contacts / for auxiliary contacts		2			
Number of NO contacts / for auxiliary contacts		0			

Switching function / a	arresting lock			Yes			
Certificates/approvals:							
General Product Approval							
(SA)	ROSTEST						
Shipping Approval					other		
ABS		Llovd's Kegister LRS	PRS	RINA	Manufacturer		
Ambient conditions:							
Protection class IP				IP65			
Ambient temperature	•						
<ul> <li>during operating</li> </ul>			°C	-25 +70			
Further information:							
Information- and Downloadcenter (Catalogs, Brochures,) http://www.siemens.com/industrial-controls/catalogs							
Industry Mall (Online ordering system) http://www.siemens.com/industrial-controls/mall							
CAx-Online-Generator http://www.siemens.com/cax							
Service&Support (Manuals, Certificates, Characteristics, FAQs,) http://support.automation.siemens.com/WW/view/en/3SE7120-1BF00/all							
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams,) http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3SE7120-1BF00							





last change:

Feb 6, 2012