

Datasheet

RS Cable Marker Application Tool for Helagrip Cable Markers Sizes B & C

RS Stock number: 404-409



Material: Cooper / Brass Alloy (Bronze) Cable Marker Application Tool Shaft

Finish: Rough PTFE (Teflon) Coating Finish for Application Tools

Contents:

1 PC – 2.0 MM (ID) Cable Marker Application Tool for "HELAGRIP" Markers A with Teflon Coating (Cable Diameter Range: 0.58 ~ 0.78 MM² / HG 1.0~ 3.0 MM) and Overall Length 66.0 MM, Diameter of Shaft – 2.70 MM, Length of Tip Chamfer – 15.0 MM, Diameter for Wire Application Hole - 2.0MM and Hole Depth - 20.0 MM) (Part No: PD-0541)

RS Item No:	Description	Application Cable	Diam	eter Range
404-405 (PD-05	42) 3.3 MM ID	Range: 0.70 ~ 4.00 M	IM ² (HG:	2.0 ~5.0 MM)
404-409 (PD-05	4.6 MM ID	Range: 4.00 ~ 16.00	MM ² (HC	3: 4.0 ~9.0 MM)

Overall Length I	Diameter of Shaft	Length of Chamfer	Diameter of Ho	ole Depth of Hole
66.0 MM 2.70	MM 15.0	MM 2.00	MM	$20.0\mathrm{MM}$
81.0 MM 4.30	MM 25.0	MM 3.30	MM	20.0 MM
87.5 MM 5.80	MM 35.0	MM 4.60	$\mathbf{M}\mathbf{M}$	20.0 MM