



Technical Data

17.01.2022

Pre-printed cable markers
WIC, snap on

WIC1-4

Article Number 561-01644



Material: Polyamide 6.6 (PA66)
Colour: Yellow (YE)

Bundle Ø min.: 2.00 mm
Bundle Ø max.: 2.80 mm
Wire Size Range (mm²): 0.50-1.50 mm²
Fixation Method: Plug in

Width (W): 5.00 mm
Height (H): 6.40 mm
Length (L): 3.0 mm

Print Method: Hotfoil printing
Marking Text: 4

Operating Temperature - °C: -40 °C to +85 °C
Flammability: UL 94 V0

Application Tool: WIC Tool



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved