

# SmartFind

---

Supported OS	OS Independent
--------------	----------------

Warranty Period	1 year
-----------------	--------

JAN	4580551573483
-----	---------------

EAN	0195713001601
-----	---------------

UPC	195713001601
-----	--------------

Warranty Type	Lenovo Warranty
---------------	-----------------

Maximum Relative Humidity (%)	90%
-------------------------------	-----

Minimum Relative Humidity (%)	8%
-------------------------------	----

Maximum Operating Temperature	35 degrees Celsius (95 degrees Fahrenheit)
Minimum Operating Temperature	0 degrees Celsius (-32 degrees Fahrenheit)
Packed Weight	384 g
Packed Dimensions (L x D x H)	107x32x221mm
Package Type	Gift box
Hardware Requirements	Supported mobile phone with USB-C charging port and Qi wireless Total output max 30W
Battery Type	Li-ion (Polymer battery)
Safety Protection	Built in Over Voltage Protection (OVP) circuit Built in Over Temperature (OTP) circuit Built in Over Current (OCP) circuit
Agency Approvals	CB,Qi,TUV, CE,UKCA, FCC,CEC,cTUVus, PSE,WPC,SIRIM,NTC,IMDA,KC,KCC,MIC,DWLF&M,NTRA,NCA,ANRT,TRA,CRA,KVALITET,TRA,RCM
Shipment Group	Lenovo Go Wireless Mobile Power Bank (10000mAh) Warranty document Quick Start Manual
Product Weight	258 g (0.57 lbs)
Height	18.5 mm (0.73 in)
Depth	72 mm (2.83 in)
Length	168 mm (6.61 in)
Special/Added Features	Up to 15W Qi wireless charging
Power Button	Yes
LED Indicator	4 LED @ 25% each 1 LED@Qi
Color	Thunder Black
Material	Plastic
Battery Charging Time	About 2 Hours (Depends on power adapter used. Value measured using Lenovo 45W power adapter)
Quick Charge	Yes
Output Power	USB-C - Max 27 W (9V/3A), Qi - Max 15 W
Charge-out Ports	1 x USB-C integrated cable 1 x USB-C port
Input Power	27 W (9V/3A)
Charge-in Ports	1 x USB-C integrated cable 1 x USB-C port
Battery Performance (Wh)	38.5 Wh

---

Battery Capacity	10000 mAh
------------------	-----------

---

Brand	Lenovo
-------	--------