

FEATURES

- Ceramic Fuse
- 6.3mm x 32mm cartridge size
- T Speed Rating
- Cylindrical in shape

RS PRO, 10A Ceramic Cartridge Fuse, 6.3 x 32mm, Speed T

RS Stock No.: 414-061



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO offer this range of miniature ceramic cartridge fuses. These fuses are anti-surge (also known as slow-blow or time-delay) which means that they allow a current to flow for a short period, without the fuse blowing/shorting. These RS PRO fuses have a high breaking capacity and are 6.3mm x 32mm.

General Specifications

Fuse Speed	T
Body Material	Ceramic
UL Class	UL 248-13
Applications	Industrial, Commercial, Home/Residential, Automotive

Electrical Specifications

Current Rating	10A
Voltage Rating	500V ac
High Rupture Capacity	Yes
Breaking Capacity (at Maximum Voltage Rating)	1500A

Mechanical Specifications

Fuse Size	6.3mm x 32mm
Overall Length	32mm
Diameter	6.3mm
Height	32mm

Approvals

Compliance/Certifications

UL

