

## LED Bulb Series



### VT-1853

#### HIGHLIGHTS :

WATTS



10

EQ. WATTS



60

LUMINOUS



806

BEAM ANGLE



200

Item No	: VT-1853
SKU Code	: 4226
Watts	: 10
EQ Watts	: 60
Base / holder	: E27
Voltage	: 220-240V,50Hz
Lumen(lm)	: 806
Color Temperature	: 4500K
Beam Angle	: 200
Commercial type	: A60
PF	: >0.5
LED Chip Type	: SMD
CRI	: >80
Energy rating label	: A+
Certification	: CE,EMC,ROHS
IP Rating Protection Class	: IP20

Body type	: THERMAL PLASTIC
Dimmable	: No
Life Time	: >20,000 Hours
Operation Temperature	: -25 ~50°C
EAN code	: 3800230626271
Unit size	: 60mm x 112mm
Packing details	: 100
Unit cbm	: 0.000474

#### PRODUCT FEATURES

- Lasts 20 times longer than Standard Bulbs
- Uses 80% less energy than Standard Bulbs
- Aluminium & Thermoplastic Body options available
- Non – Flickering
- Widely used in Residential Lighting.
- LED Bulbs are the best replacement for conventional Incandescent or Fluorescent Bulbs
- Smart choice for the conventional look
- Looks are deceptive in this case
- LED innovation made to look like a traditional bulb

[CLICK HERE](#)  
FOR OTHER RELATED CERTIFICATES 