Data sheet

HP Stereo USB Headset G2





Sounds good? Sounds great

Hop on and hop off calls all day long without ever losing a beat. Plug right in and get ready to speak and hear clearly all day. With noise-cancelling, comfortable design, and easy adjustment, your sound comfort will carry you from call to call without interference or frustration.

Control the Call

Hop on any call with ease. The flexible boom mic blocks the background noise to keep your call focused. The in-line volume control and mute keeps you in control of your environment.

Snug and Comfortable

These durable vegan leather earcups are designed for all-day comfort. Just adjust the head strap to be perfectly snug so you can hop on and off calls all day without soreness.

Simple USB-A Connection

A simple USB-A plug will have you on the call in seconds with a connection that won't glitch out or lose power.

Works With Chromebook Certified

The Works With Chromebook badge on a device means it's optimized to work¹ with your Chromebook and other Chrome OS devices². Enjoy a seamless experience across Works With Chromebook certified accessories². Look for the Works With Chromebook badge and rest assured that it'll all work together³.

- 1. Gmail account required for full functionality
- 2. Google tested to meet Chromebook compatibility standards.
- 3. This product works with devices capable of running the latest version of Chrome OS and has been certified to meet Google's compatibility standards. Google is not responsible for the operation of this product or its compliance with safety requirements. Chromebook and the Works With Chromebook badge are trademarks of Google LLC.

Specifications



HP Stereo USB Headset G2

Part number		428H5AA#ABL 428K6AA
Dimensions (HxWxD)		6.3 x 5.79 x 2.17 in (160 x 147 x 55 mm)
Weight		3.35 oz (95 g)
Cable length		5.9 ft (1.8 M)
Speaker driver	Dynamic speaker drivers	φ30±0.2 mm
	Sensitivity	120dB±3dB at 1KHz/1mW
	Frequency response	20Hz-20KHz
	Impedance	64 0hm±15%
Microphone	Sensitivity	-38±3dB
	Frequency response	100Hz – 10KHz
	Impedance	≤2.2K 0hm
	Туре	Uni-Directional Uni-Directional
	SNR	60dB
System requirements		USB-A Port
Compatibility		Windows® 10, Windows® 11, macOS® , Chrome OS™
What's in the box		HP Stereo USB Headset G2, Manual (QSP), Warranty
Warranty		HP standard one-year limited warranty
Country of origin		China

Additional information

UPC code	196337982499
Tariff number	10196337982496
Master carton UPC code	10195908812484
Master carton quantity	40
Master carton dimensions	15.12 x 12.13 x 22.83 in (384 x 308 x 580 mm)
Master carton weight	17.28 lb (7.84 kg)
Packaged product dimensions (HxWxD)	6.7 in x 5.67 in x 2.13 in (170 x 144 x 54 mm)
Unpackaged product dimensions (HxWxD)	6.49 x 5.118 x 1.968 in (165 x 130 x 50 mm) (not including boom mic)
Packaged product weight	0.47 lb (0.21 kg)
Unpackaged product weight	0.21 lb (0.095 kg)
Pallet configuration Total weight	536.16 lb / 243.0 kg
Cartons per layer	6
Layers	5
Cartons per pallet	30
Products per layer	240
Total products per pallet	1200

Sign up for updates hp.com/go/getupdated











Share with colleagues

Rate this document

© Copyright 2022 The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

HP includes a one-year/ two-year limited warranty with online support available 24x7. Consult the HP Customer Support Center for details, or go to www. hp.com/go/orderdocuments. Internet access required and not included.

