


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0430250400**  
**Status:** **Active**  
**Overview:** Micro-Fit Connector System  
**Description:** Micro-Fit 3.0 Receptacle Housing, Dual Row, 4 Circuits, UL 94V-0, Low-Halogen, Black

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Test Summary TS-43045-001-001 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Test Summary TS-46235-001-001 (PDF)</a>
<a href="#">Application Specification 430250000-AS-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Packaging Specification PK-43025-001-001 (PDF)</a>	<a href="#">Product Literature (PDF)</a>



**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	Crimp Housings
Series	<u>43025</u>
3D Viewer	Yes
Application	Power, Wire-to-Board, Wire-to-Wire
Overview	<u>Micro-Fit Connector System</u>
Product Literature Order No	987650-5984
Product Name	Micro-Fit 3.0
UPC	800754315234

**Physical**

Circuits (maximum)	4
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.422/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Application Specification	430250000-AS-000
Packaging Specification	PK-43025-001-001
Sales Drawing	430250000-SD-000
Test Summary	TS-43045-001-001, TS-46235-001-001

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

43025 Series

**Mates With**

Micro-Fit 3.0 Plug Housings 43020 , Micro-Fit 3.0 Headers 43045 , Micro-Fit 3.0 Test Plug 44242

**Use With**

Micro-Fit 3.0 Female Crimp Terminals 43030 , 45773 , Micro-Fit RMF Female Crimp Terminals 46235