

FEATURES

- Made of recyclable Polypropylene
- Shapely and solid locks
- Large decoration area for IML and screen printing
- Sturdy plug-in hinges
- Stable and robust case feet
- Ergonomic, convenient design handle
- Foam inserts
- Grey in colour
- Stacking feet to enable safe and easy stacking

RS PRO Waterproof Plastic Equipment case, 230 x 275 x 83mm

RS Stock No.: 435-9693



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS Pro Tekno Cases offer a fusion of high-level functionality and modern design. RS Pro Tekno cases offer protection for sensitive products and combined with individual foam inlays and/or deep-drawn inserts guarantee a maximum protection and a practical arrangement of the content

General Specifications

Material	PP
Foam	Yes
Watertight or Waterproof	No
Wheels	No
Colour	Grey
Dividers	No
Finish	Textured; Smooth
Lockable	Yes
Hazardous Area Certification	ATEX; Class I
Material Type	Plastic
Applications	Medical Technology; Pharmaceutical, Dental; Measuring Instruments; Optics and Precision Mechanics sectors; Musical instruments; Tools; Cable equipment; Photography and Camera Equipment; Test equipment; Component storage, Electronics, Audio Video equipment
Rack Rail	Yes

Mechanical Specifications

Internal Height	175mm
Internal Width	261mm
Internal Depth	77mm
Internal Dimensions	175x261x77mm
External Height	230mm
External Width	275mm
External Depth	83mm
External Dimensions	230x275x83mm
Weight	3.1; 8; 20kg
Up to	40kg
Volume	239l
Thickness Of Aluminium Sheet	1mm
Reinforced	3
Lid Depth	45mm

Operation Environment Specifications

Temperature	-20 to 80°C
-------------	-------------

Protection Category

IP Rating	IP54; IP65; IP67; IPX5
-----------	------------------------

Approvals

Compliance/Certifications	CE / UR / cUR
---------------------------	---------------

