


## LED Bulb Series



### VT-1969

#### HIGHLIGHTS :

WATTS



7

EQ. WATTS



45

LUMINOUS



550

BEAM ANGLE



110

Item No	: VT-1969
SKU Code	: 4438
Watts	: 7
EQ Watts	: 45
Base / holder	: PAR Gx53
Voltage	: 220-240V,50Hz
Lumen(lm)	: 550
Color Temperature	: 4500K
Beam Angle	: 110
Commercial type	: ROUND
PF	: >0.5
LED Chip Type	: SMD
CRI	: >80
Energy rating label	: A+
Certification	: EMC,LVD,ROHS
Body type	: THERMAL PLASTIC
Dimmable	: No
Life Time	: 20,000 Hours
Operation Temperature	: -20~50'C
EAN code	: 3800157607049
Unit size	: 75 x 23.5 mm
Packing details	: 200
Unit cbm	: 0.001482

#### PRODUCT FEATURES

- Lasts 20 times longer than Standard Bulbs
- Uses 80% less energy than Standard Bulbs
- Aluminium & Thermoplastic Body options available
- Non – Flickering
- Widely used in Residential Lighting.
- LED Bulbs are the best replacement for conventional Incandescent or Fluorescent Bulbs
- Smart choice for the conventional look
- Looks are deceptive in this case
- LED innovation made to look like a traditional bulb

[CLICK HERE](#)  
FOR OTHER RELATED CERTIFICATES