

LED Bulb Series



VT-2017

HIGHLIGHTS :

WATTS



17

EQ. WATTS



125

LUMINOUS



1800

BEAM ANGLE



200

Item No	: VT-2017
SKU Code	: 4456
Watts	: 17
EQ Watts	: 125
Base / holder	: E27
Voltage	: 220-240V,50Hz
Lumen(lm)	: 1800
Color Temperature	: 2700K
Beam Angle	: 200
Commercial type	: A65
PF	: >0.5
LED Chip Type	: SMD
CRI	: >80
Energy rating label	: A+
Certification	: EMC,LVD,ROHS
Body type	: THERMAL PLASTIC
Dimmable	: No
Life Time	: 20,000 Hours
Operation Temperature	: -20~50'C
EAN code	: 3800157608121
Unit size	: 65mm x 130mm
Packing details	: 100
Unit cbm	: 0.000714

PRODUCT FEATURES

- Lasts 20 times longer than Standard Bulbs
- Uses 80% less energy than Standard Bulbs
- Aluminium & Thermoplastic Body options available
- Non – Flickering
- Widely used in Residential Lighting.
- LED Bulbs are the best replacement for conventional Incandescent or Fluorescent Bulbs
- Smart choice for the conventional look
- Looks are deceptive in this case
- LED innovation made to look like a traditional bulb

[CLICK HERE](#)
FOR OTHER RELATED CERTIFICATES