

FEATURES

- Curved jaw for effective shearing action on copper wires
- Moulded handle grip
- Spring return jaws
- Safety catch to lock jaws closed

RS PRO 165mm Straight Cutters

RS Stock No.: 450-3496



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Cutters



Product Description

From the trusted RS PRO, these cable cutters are suitable for cutting copper wire and other light-duty applications. They feature a curved jaw that provides an excellent shearing action on copper wires and other materials. The cutters also feature a safety catch that allows for the jaws to be locked in place when not in use.

General Specifications

Туре	Straight Cutters
Applications	Cutting copper wire, wood sticks, cardboard, rope,
	plastic cards and fabrics

Mechanical Specifications

Overall Length	165mm
Jaw Length	13mm
Material	Stainless steel sheet (sus# 420-j2) for pliers, sus# 320 for rivet, spring steel for tension return spring, p.p injection handle
Maximum Cutting Capacity	3.0mm
Hardness	Heat treated to hrc: 50-54 degree (body)
Finish	Grinding cutting edge, polish finish

Cutters



