# ECH® Product DATASHEET

# Mini Thermo-Anemometer Series

Pocket Air Velocity meters with displays of Temperature, Relative Humidity and Dew Point

## **Common Features:**

- Fold up protective housing extends to 9" for better reach
- · Large dual display of air velocity and temperature
- · Data Hold to freeze most recent display
- Auto shutoff 20 minutes after last key is pressed
- Water resistant housing floats and Drop tested to 6 feet
- · Complete with CR2032 lithium battery and lanyard

#### **Windspeed**

- Measures ft/min, MPH, m/s, km/h, Knots and Beaufort Force
- Selectable averaging function of 5, 10, or 13 second intervals
- Replaceable non-corrosive plastic wind vane (impeller)

#### **Temperature & Windchill**

• Measures from 0 to 122°F (-18 to 50°C)

#### **Model 45158 Additional Features**

#### **Relative Humidity and Dew Point**

- Dual display of air velocity and relative humidity
- Measures RH from 10% to 95%
- Measure Dew Point from 32°F to 122°F



Model 45158 with Temperature + Humidity

# $\epsilon$

Measurements	Range	Resolution	Basic Accuracy
ft/min (feet per minute):	100 to 5500 ft/min	20ft/min	± (3%rdg + 40ft/min)
m/s (meters per second):	0.5 to 28m/s	0.1m/s	± (3%rdg + 0.2m/s)
km/h (kilometers per hour):	1.8 to 100.6 km/h	0.7km/h	± (3%rdg + 1.4km/h)
MPH (Miles per hour):	1.1 to 62.5 MPH	0.2MPH	± (3%rdg + 0.4MPH)
knots (nautical miles per hour):	1.0 to 54.3 knots	0.3knots	± (3%rdg + 0.6knots)
Beaufort Force:	1 to 17 BF	1 BF	± 1
Temperature:	0 to 122°F (-18 to 50°C)	0.1°F/°C	±1.8°F/±1°C
Relative Humidity: (Model 45158)	10% to 95%	1%	± 4%
Dew Point : (Model 45158)	32°F to 122°F	1°	± 2%
Power:	CR2032 Lithium battery		
Dimensions:	5.25x2.75 x 0.75" (133 x 70 x 19mm)		
Vane:	1"(24mm) diameter	•	
Weight:	3oz (95g)		

## **Ordering Information:**

45118	Mini Thermo-Anemometer with Temperature	\$89.99
	Mini Thermo-Anemometer+ w/ Temp+Humidity .	
45119	Spare Mini Impeller Assembly	\$15.99
<b>CA895</b>	Vinyl Pouch Carrying Case	\$10.99

**EXTECH INSTRUMENTS CORPORATION** 285 Bear Hill Road, Waltham, MA 02451-1064, U.S.A. Phone: 781-890-7440 • FAX 781-890-7864

"Make mine an Extech!"" www.extech.com

