

FEATURES

- Inline fuse holder with pull-up latch
- Tinned Brass inserts
- Screw Mounting type
- Screw Down termination

RS PRO Fused, 3 Way, Nylon Fused Terminal Block, 250V

RS Stock No.: 452-625



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO fused panel mount terminal block features an integrated in-line fuse holder. The white housing is made from nylon with tinned brass inserts for a screwed termination. A pull-up latch enables an easy replacement of a fuse.

Options include:

452-619 - 3 way fused terminal block, 16A

452-625 - 3 way fused terminal block, 10A

General Specifications

Fused	Yes
Mounting Type	Screw Mount
Termination Method	Screw Down
Material	Nylon
Number of Ways	3
Applications	Sound equipment, Electrical installations, Surge protectors, Public address systems for speakers and other inputs and outputs, Electrical wiring to connect switches, Major appliances

Electrical Specifications

Current Rating	10A
Voltage Rating	250V

Mechanical Specifications

Cable CSA	6mm ²
------------------	------------------

Operation Environment Specifications

Maximum Operating Temperature

100°C

