



ENGLISH

Datasheet

Stock No: 458-367

RS Pro Mechanical HVAC Thermostat, RS Pro, SPCO 10 A, 4 A



Product Details

Thermostats with SPCO contacts

Thermostats that can switch between heating and cooling units.

Surface mounting suitable for industrial and commercial applications

Snap action switch with change over contacts

Shunt accelerator minimises overshoot

Dial can be set for max/min settings

Switching differential 0.5°C

Specifications:

Switch Configuration	SPCO
Contact Rating	4 A, 10 A
Supply Voltage	230 V ac
Maximum Temperature	+30 °C
Minimum Temperature	+5 °C
Temperature Range	+5 → +30 °C