

ENGLISH

Datasheet

RS Pro Non-Fused Terminal Block, 3 Way/Pole, 4 mm², Nylon, 450 V

RS Stock No: 469-1795



Product Details

RS Pro non-fused terminal block is suitable for use with circular profile cables for indoors or outdoors. This versatile cable connector is IP68 rated, it means it can be used underwater or underground. The internal terminal block is easily accessible and quickly wired. This 3-way block comes with metal mounting clip. The cable mount block has 2-part gland body sealing ring that allows the use of a wide cable diameter range. This terminal block with 4 mm², is made of nylon material. The block with 450 V voltage rating, has brass contact with nickel plating.

Features and Benefits

- Tested to IP68 at 5 bar
- Temperature range from -20 to +125°C
- Rated at 450 V/32 A
- Barrel in nylon 66 with cable gland and terminal block in nylon
- 115 mm (3-pole), 130 mm (5-pole) long
- Diameters 26.5 mm and 32 mm respectively
- Cable gland size M20 (3-pole), M25 (5-pole)



ENGLISH

Specifications:

Brass
Nickel
32 A
Yes
Nylon
+125°C
-40°C
Cable Mount
3
450 V
4 mm²
Black
RoHS Compliant