

ENGLISH

Datasheet Non-Fused Terminal Block, 5 Way, Nylon, 450 V

RS Stock 469-1818



Specifications:

- Low cost waterproof connector
- For use with circular profile cables
- Indoor or outdoor use
- Ready to use kit
- Test4ed t IP at 5 bar
- Can be used under water / underground
- Compact design
- Wide cable range

Component	Material	Temperature Rating	Colour
Barrel Solid colours	PA 66 UL 94 V0	-20 to +125°C	Black (Standard) Grey (Option)
Translucent colours	Polycarbonate	-20 to +110 ⁰ C	Red, Green, Orange, Clear
Cable Glands	PA6 Nylon	-20 k o +100°C	Black (Standard) Grey (Option)
Sealing Ring	Neoprene (CR)	-20 to +100°C	Black
Connector	PA 66 UL 94 V0	-20 to +125°C	Black
Connector Inserts	Nickel Plated Brass	N/A	N/A