

FEATURES

- Zinc Plated mild steel finger operated jack screw
- Finger Operated Jack screw, 5 mm Dia. 59 mm Length
- 4-40UNC Thread
- Steel material with zinc finish
- Screw for D sub connectors

RS PRO Jack Screw Screw down Cover

RS Stock No.: 470-522



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Zinc-plated mild steel jack screws for use with screw down covers (covers not supplied). These types of jack screws can be used to hold D-sub connectors together. When unscrewed, they allow the connector halves to be taken apart. These small jack screws have screw heads that enable the user's fingers to turn the jackscrew. The head can have an internal female thread, with the male externally threaded screw shaft extending from that.

General Specifications

Accessory Type	Jack Screw
For Use With	Screw Down Cover
Material	Steel
Finish	Zinc
Thread Size	4-40 UNC
Application	Preventing mechanical stress, provide EMI/RFI shielding and protection from the elements, Industrial, commercial and domestic applications and environments

Mechanical Specifications

Overall Length	60mm
-----------------------	------

Approvals

Compliance/Certifications	2011/65/EU and 2015/863
----------------------------------	-------------------------

