

FEATURES

- No software or drivers needed
- Functions can be set by internal dip switches
- Multi keystroke functions available on each switch
- 2.5m cable
- Power consumption 5V @ 25mA
- Weight 395g
- Hands free control

RS PRO Light Industrial Momentary USB programmable foot switch - Glass Fibre Reinforced Polymer Case Material, Single

RS Stock No.: 474-537



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description ATTRIBUTE 1

RS PRO USB programmable foot switch which works with Windows, Linux and Mac operating systems. Foot switches are commonly used on machinery where hand operated switches are a safety concern. This foot controller pedal is ideal for light industrial applications.

General Specifications

Contact Configuration	Single Pole Single Throw (SPST)
Switch Operation	Momentary
Case Material	Glass Fibre Reinforced Polymer
Switch Environment	Light Industrial
Guard Cover	No
Colour	Black
Applications	Foot switches are commonly used in applications where hands-free control is more practical or safer. They can be found on: Industrial machinery and smaller power tools, Hospital beds, Dentist Chairs, Lamps
Cable Connection	2.5M CABLE LENGTH AS STANDARD

Electrical Specifications

Contact Voltage Rating (AC)	5V
Contact Current Rating	25mA @ 5V ac

Mechanical Specifications

Length	141mm
Height	40mm
Dimensions	141mm x 105mm x 40mm
Width	105mm

Protection Category

IP Rating	IPX2
-----------	------

Approvals

Standards Met	2014/35/EU, EN 60950
Compliance/Certifications	RoHS



