

Datasheet

ENGLISH

8P 270 DIN Socket Panel Screw Mount

RS Stock number 491-140



Specifications:


Rating: 100V AC 4A max.


Contact Resistance: pins- $30m\Omega$ max; shell-50m Ω max.


Insulation Resistance: $100M\Omega$ min. at 500V DC

Dielectric Strength: 250V AC R.M.S. for 1 minute

Dimensions(mm)









RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.



ENGLISH





Through Hole Dimension

| No. | Description | Material | Treat |
|-----|------------------|----------|-------------|
| 1 | Shield Cover | Zn Alloy | Chrome Ptd. |
| 2 | Negative Contact | Copper | Nickel Ptd. |
| 3 | 8P 270 Housing | ABS | |
| 4 | Terminals | Brass | Silver Ptd. |
| 5 | Screw Nut | Brass | Nickel Ptd. |