

LED Panel Series



VT-2222

HIGHLIGHTS :

WATTS



22

EQ. WATTS



120

LUMINOUS



2200

BEAM ANGLE



110

Item No	: VT-2222
SKU Code	: 4937
Watts	: 22
EQ Watts	: 120
Voltage	: AC:220-240V,50/60Hz
Lumen(lm)	: 2200
Color Temperature	: 3000K
Beam Angle	: 110
Commercial type	: ROUND
PF	: >0.9
LED Chip Type	: SMD
CRI	: >80
Energy rating label	: A+
Certification	: EMC,LVD,ROHS
Body type	: DIE CAST ALUMINUM
Dimmable	: No
Life Time	: 20,000 Hours
Operation Temperature	: -20~50'C
EAN code	: 3800157606530
Unit size	: D:170x27mm
Cutting size	: 160mm
Packing details	: 40
Unit cbm	: 0.001103

PRODUCT FEATURES

- Compare with incandescent, it can save over 80% electric cost
- Contemporary & Elegant Design
- Higher Light Transmission Rate
- No flickering, No U.V Radiation
- No Lead or Mercury content hence Environment friendly
- Suitable for office and genral lighting (Conference Room, Showroom, lobby, cabin, kitchen etc.)
- High quality power driver
- Instant light 100% O s
- Temp -20 to + 45'C

[CLICK HERE FOR OTHER RELATED CERTIFICATES](#) 