

Set of Circlip Pliers

4 parts

00
19

- > Tool roll made of hard-wearing polyester fabric
- > With practical, adjustable quick release fastener

00 19 56 V01

Four common Circlip Pliers for internal and external circlips

00 19 57 V01

Four common Precision Circlip Pliers for highest requirements



00 19 56 V01
⊙ ⊙



00 19 57 V01
⊙ ⊙

Article No.	EAN 4003773-			Style	Capacity Ø mm	Tips Ø mm	Quantity	⚖ g
00 19 56 V01	081548		Set of Circlip Pliers, 4 parts					615
		⊙	44 11 J1	Circlip Pliers for internal circlips in bore holes	straight tips	12 - 25	1.3	1
		⊙	44 11 J2			19 - 60	1.8	1
		⊙ MM	46 11 A1		Circlip Pliers for external circlips on shafts	10 - 25	1.3	1
		⊙ MM	46 11 A2			19 - 60	1.8	1
00 19 57 V01	081555		Precision Circlip Pliers Set 4 parts					871
		⊙	48 11 J2	Precision Circlip Pliers for internal circlips in bore holes	straight tips	19 - 60	1.3	1
		⊙ ∠90°	48 21 J21		angled tips	19 - 60	1.8	1
		⊙ MM	49 11 A2	Precision Circlip Pliers for external circlips on shafts	straight tips	19 - 60	1.3	1
		⊙ ∠90° MM	49 21 A21		angled tips	19 - 60	1.8	1

Set of Circlip Pliers

8 parts

00
19

- > Tool roll made of hard-wearing polyester fabric
- > With practical, adjustable quick release fastener

00 19 58 V01

Eight established models of circlip pliers for internal and external circlips

00 19 58 V02

Eight established models of precision circlip pliers for the most demanding requirements



00 19 58 V01
⊙ ⊙



00 19 58 V02
⊙ ⊙

Article No.	EAN 4003773-			Style	Capacity Ø mm	Tips Ø mm	Quantity	⚖ g
00 19 58 V01	081562		Set of Circlip Pliers, 8 parts					1156
		⊙	44 11 J1	Circlip Pliers for internal circlips in bore holes	straight tips	12 - 25	1.3	1
		⊙	44 11 J2			19 - 60	1.8	1
		⊙ ∠90°	44 21 J11		angled tips	12 - 25	1.3	1
		⊙ ∠90°	44 21 J21			19 - 60	1.8	1
		⊙ MM	46 11 A1	Circlip Pliers for external circlips on shafts	straight tips	10 - 25	1.3	1
		⊙ MM	46 11 A2			19 - 60	1.8	1
		⊙ ∠90° MM	46 21 A11		angled tips	10 - 25	1.3	1
		⊙ ∠90° MM	46 21 A21			19 - 60	1.8	1
00 19 58 V02	081579		Precision Circlip Pliers Set, 8-parts					1357
		⊙ MM	48 11 J1	Precision Circlip Pliers for internal circlips in bore holes	straight tips	12 - 25	1.3	1
		⊙ MM	48 11 J2			19 - 60	1.8	1
		⊙ ∠90° MM	48 21 J11		angled tips	12 - 25	1.3	1
		⊙ ∠90° MM	48 21 J21			19 - 60	1.8	1
		⊙ MM	49 11 A1	Precision Circlip Pliers for external circlips on shafts	straight tips	10 - 25	1.3	1
		⊙ MM	49 11 A2			19 - 60	1.8	1
		⊙ ∠90° MM	49 21 A11		angled tips	10 - 25	1.3	1
		⊙ ∠90° MM	49 21 A21			19 - 60	1.8	1