



TRANSFORMER SITAS; PHASES:1;
 PN/PN(S6)(KVA):0,25 /0,85; UPRI(V):230+/-5%;
 USEC(V):42; ISEC(A):5,95; F(HZ):50...60; VECTOR
 GR./SHIELD WNG.:li0 /0; TA/ISOKL:40 /B; IP00; TYPE
 OF TERMINALS:SCREW/TAB CONNECTION;
 INSTALLATION:SCREWS/MOUNTING RAILS; EN
 61558-2-2, -2-6 >UL/CSA-RECOGNIZED< >CONTROL
 CIRCUIT TRANSFORMER< >SAFETY ISOLATING
 TRANSFORMER<

Figure similar

General technical data:		
Product designation		transformer SITAS
Product brand name		SIDAC
Operating apparent output rated value	V·A	250
Efficiency		0.89
Connection method for transformers		li0
Certificate of suitability		CE / cRUus
Product function		
• Temperature monitoring		No
• Insulation monitoring		No
• Short-circuit and overload proof		No
Number of shielding windings		0
Short-term vector power	V·A	850
Relative short-circuit voltage	%	5.4
Inputs:		
Phase number of the inputs		1
Input voltage		

• _1 rated value	V	242
• _2 rated value	V	230
• _3 rated value	V	218
Electrical input frequency		
• minimum	Hz	50
• maximum	Hz	60

Outputs:		
Phase number of the outputs		1
Output voltage		
• _1 rated value	V	24
Electrical output frequency		
• maximum	Hz	60
• minimum	Hz	50

Ambient conditions:		
Thermal class acc. to IEC 60085		B
Ambient temperature rated value	°C	40
Protection class IP		IP00

Mechanical data:		
Type of electrical connection		
• at output for main current circuit		screw-type terminals / tab terminals
• at input for main current circuit		screw-type terminals / tab terminals
Mounting type		screws / standard rail
Construction form of the iron core		EI 96/58
Width	m	0.098
Height	m	0.106
Depth	m	0.118

Certificates/ approvals:			
General Product Approval	Declaration of Conformity	Shipping Approval	other



EG-Konf.

[Miscellaneous](#)



PRS

[Confirmation](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AM4042-4TV00-0EA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4AM4042-4TV00-0EA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AM4042-4TV00-0EA0&lang=en

last modified:

01/20/2019