

PRODUCT-DETAILS

# UPS PowerValue 11LI Up 600 VA

## UPS PowerValue 11LI Up 600 VA



### General Information

Extended Product Type	UPS PowerValue 11LI Up 600 VA
Product ID	4NWP100170R0001
EAN	7640169262609
Catalog Description	UPS PowerValue 11LI Up 600 VA
Long Description	VI UPS PowerValue 11LI Up 600VA/360W;230V;50/60Hz;simulated sinewave;2 min

### Circular Value

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD004620
RoHS Information	4NWD004317
SCIP	221d0688-aae7-414c-9217-381526c61e7a Switzerland (CH)
Simplified SCIP	ce3fb638-aaf8-4e0a-9f81-4a0bd8aa35ba Netherlands (NL) a021d7c5-cee2-4ad2-bbb4-a52e17eb6feb Spain (ES) e6c4e29e-3159-4376-9926-41d46df53b87 Netherlands (NL) e504bb93-2b18-4d0a-8c5e-82f9d5b0a141 Germany (DE) e157c111-5839-4542-8703-cb5ce78de44b Denmark (DK) 51637fdd-f1b8-42d2-b695-218ff3b1bc08 Poland (PL) 9c84a092-5af6-4bf7-b098-f7e555438e7b Norway (NO) 97edee7c-bf7d-4830-8803-303e740213b7 Finland (FI) 98087d92-d78f-4a15-8a7f-41e342795220 Netherlands (NL) 4ec9d11a-f107-4a42-ba58-03a21e8d89e4 Germany (DE) 29d298b2-f974-4a3f-8022-4fadac902b63 Croatia (HR) 4d4bf0ee-8f86-4180-b21d-195847446fb8 Czech Republic (CZ)

26df521e-3ac6-4047-9c0a-38f384611633 Poland (PL)  
 adb29e63-7cdb-440c-801f-fc201d06eb2 Netherlands (NL)  
 1d378ca1-10e6-437e-8aeb-b269a4f7032b Netherlands (NL)  
 391a8928-4250-441d-8ca2-00488f457c75 Estonia (EE)  
 9dd4cd21-ea48-45b8-b95f-bd0236f5402e Greece (GR)  
 66134fc4-282b-4be2-9188-61af5b84b184 Portugal (PT)  
 bda32812-ba73-4377-8f94-12c90ea2dc6e Bulgaria (BG)  
 7cb1c10d-93ed-4ee9-9e01-7b2790b15f62 Sweden (SE)  
 44c8a55b-8bc4-4391-8a20-5e9eec4e7a40 France (FR)  
 3880375a-c5e9-4550-bd17-bb4c0a2df909 Sweden (SE)  
 81bbe73c-26f4-488e-83b3-90bf32abd8b2 Poland (PL)  
 4500b888-1892-4cb0-aa3b-3254604ebc7a Germany (DE)  
 9a8a72b1-6896-4553-9a46-231a6d2835cb Germany (DE)  
 3cfb7c9e-7ff6-4d97-9379-56028801430a France (FR)

## Environmental

Ambient Air Temperature	Storage -15...+60 °C
RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	No declaration needed
SCIP	221d0688-aae7-414c-9217-381526c61e7a Switzerland (CH)
Simplified SCIP	ce3fb638-aaf8-4e0a-9f81-4a0bd8aa35ba Netherlands (NL) a021d7c5-cee2-4ad2-bbb4-a52e17eb6feb Spain (ES) e6c4e29e-3159-4376-9926-41d46df53b87 Netherlands (NL) e504bb93-2b18-4d0a-8c5e-82f9d5b0a141 Germany (DE) e157c111-5839-4542-8703-cb5ce78de44b Denmark (DK) 51637fdd-f1b8-42d2-b695-218ff3b1bc08 Poland (PL) 9c84a092-5af6-4bf7-b098-f7e555438e7b Norway (NO) 97edee7c-bf7d-4830-8803-303e740213b7 Finland (FI) 98087d92-d78f-4a15-8a7f-41e342795220 Netherlands (NL) 4ec9d11a-f107-4a42-ba58-03a21e8d89e4 Germany (DE) 29d298b2-f974-4a3f-8022-4fadac902b63 Croatia (HR) 4d4bf0ee-8f86-4180-b21d-195847446fb8 Czech Republic (CZ) 26df521e-3ac6-4047-9c0a-38f384611633 Poland (PL) adb29e63-7cdb-440c-801f-fc201d06eb2 Netherlands (NL) 1d378ca1-10e6-437e-8aeb-b269a4f7032b Netherlands (NL) 391a8928-4250-441d-8ca2-00488f457c75 Estonia (EE) 9dd4cd21-ea48-45b8-b95f-bd0236f5402e Greece (GR) 66134fc4-282b-4be2-9188-61af5b84b184 Portugal (PT) bda32812-ba73-4377-8f94-12c90ea2dc6e Bulgaria (BG) 7cb1c10d-93ed-4ee9-9e01-7b2790b15f62 Sweden (SE) 44c8a55b-8bc4-4391-8a20-5e9eec4e7a40 France (FR) 3880375a-c5e9-4550-bd17-bb4c0a2df909 Sweden (SE) 81bbe73c-26f4-488e-83b3-90bf32abd8b2 Poland (PL) 4500b888-1892-4cb0-aa3b-3254604ebc7a Germany (DE) 9a8a72b1-6896-4553-9a46-231a6d2835cb Germany (DE) 3cfb7c9e-7ff6-4d97-9379-56028801430a France (FR)

## Technical

Input Voltage ( $U_{in}$ )	230 V
Input Voltage Type	AC
Rated Frequency (f)	Primary 50 Hz Primary 60 Hz Secondary 50 Hz Secondary 60 Hz
Apparent Power Output	600 V·A
Rated Output Power	360 W
Communication Interface	USB, RS-232
Number of Phases	Primary - 1 Secondary - 1
Number of Outputs	C13 Connection 4
Connection Type	IEC C14
Display Type	LCD
Options Provided	Auto shut down function
Battery Chemical Composition	Lead-Acid

Battery Type	Portable
Battery Weight	2.1 kg
Number of Batteries	1

## Dimensions

Product Net Width	122 mm
Product Net Height	160 mm
Product Net Depth / Length	315 mm
Product Net Weight	4.1 kg

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	197 mm
Package Level 1 Height	250 mm
Package Level 1 Depth / Length	395 mm
Package Level 1 Gross Weight	5.3 kg
Package Level 1 EAN	7640169262609

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044000
Country of Origin	China (CN)

## Certificates and Declarations

Declaration of Conformity - CCC	No certification needed
Declaration of Conformity - CE	4NWD004317

## Popular Downloads

Data Sheet, Technical Information	4NWD004445_ML
Instructions and Manuals	4NWD004445_ML
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658

## Classifications

ETIM 7	EC000382 - UPS
ETIM 8	EC000382 - UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000
eClass	V11.1 : 27040690

---

Object Classification Code

G

---

---

## Categories

---

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 LI IEC 230V

