

PRODUCT-DETAILS

UPS PowerValue 11LI Up 800 VA

UPS PowerValue 11LI Up 800 VA



General Information

Extended Product Type	UPS PowerValue 11LI Up 800 VA
Product ID	4NWP100171R0001
EAN	7640169262616
Catalog Description	UPS PowerValue 11LI Up 800 VA
Long Description	VI UPS PowerValue 11LI Up 800VA/480W;230V;50/60Hz;simulated sinewave;1.5 min

Circular Value

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD004620
RoHS Information	4NWD004317
SCIP	a670f830-777f-4b36-b3b0-267df370e80a Switzerland (CH)
Simplified SCIP	cc87875c-838e-4faa-b144-5fae77325bb1 France (FR) e05dd807-5001-4b25-82d6-78c0b3c6442a Netherlands (NL) 466b05c1-678f-407a-9295-3cd8430b9d5f Spain (ES) 047359aa-beeb-4a20-91cf-85a491b0be35 Netherlands (NL) cad3f8af-3f58-4603-a27f-54eea6e1929b Germany (DE) 0974efaa-b231-4051-959f-c9372753c053 Denmark (DK) d0922cc9-831f-4d0a-917f-e6f8f59c7687 Poland (PL) 23d84147-e808-42fc-a46c-1a178eca51ed Norway (NO) 21c7005d-4646-4e54-bd8e-ac0c43883bad Finland (FI) 9d15a7f5-9796-4d2d-ad56-e1310e7f1613 Netherlands (NL) 47d1b636-33a3-4de7-bf3a-7fa44205909e Germany (DE) 8127a87e-3635-4762-a944-d1e413bda66c Croatia (HR)

9512417d-4dd0-42dd-85a6-2bad9a2c5227 Czech Republic (CZ)
 ebbcdac6-d783-4ef6-aec2-bb6cd4eb5d4b Poland (PL)
 9c4145ac-9701-42eb-a9b7-96a1bda4642c Netherlands (NL)
 34979ea6-1d69-42bb-9f04-d92e604756b5 Netherlands (NL)
 601eb18e-71f9-4bab-97a2-d671fb148cd7 Estonia (EE)
 fc2c0b97-494f-4a2b-aa3d-066f3304fca2 Greece (GR)
 90e38c19-0883-4c5d-8120-cba054768065 Portugal (PT)
 5b8264e6-3628-41f1-a0a8-ba6d837e0f5a Bulgaria (BG)
 f8372a36-bb14-4f2e-81c8-3180ab69367c Sweden (SE)
 341ca2ee-895e-4563-b591-272733f2f06b France (FR)
 0ab4f341-db89-41d2-8f72-8d45b8421388 Sweden (SE)
 7eba0fb8-cd03-4e10-a726-06883cfc36b4 Poland (PL)
 380e1957-1bbb-40f2-aa62-e2c21ca3fee5 Germany (DE)
 1b37528a-776b-46b9-bea8-5ee1c305a03b Germany (DE)

Environmental

Ambient Air Temperature	Storage -15...+60 °C
RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	No declaration needed
SCIP	a670f830-777f-4b36-b3b0-267df370e80a Switzerland (CH)
Simplified SCIP	cc87875c-838e-4faa-b144-5fae77325bb1 France (FR) e05dd807-5001-4b25-82d6-78c0b3c6442a Netherlands (NL) 466b05c1-678f-407a-9295-3cd8430b9d5f Spain (ES) 047359aa-beeb-4a20-91cf-85a491b0be35 Netherlands (NL) cad3f8af-3f58-4603-a27f-54eea6e1929b Germany (DE) 0974efaa-b231-4051-959f-c9372753c053 Denmark (DK) d0922cc9-831f-4d0a-917f-e6f8f59c7687 Poland (PL) 23d84147-e808-42fc-a46c-1a178eca51ed Norway (NO) 21c7005d-4646-4e54-bd8e-ac0c43883bad Finland (FI) 9d15a7f5-9796-4d2d-ad56-e1310e7f1613 Netherlands (NL) 47d1b636-33a3-4de7-bf3a-7fa44205909e Germany (DE) 8127a87e-3635-4762-a944-d1e413bda66c Croatia (HR) 9512417d-4dd0-42dd-85a6-2bad9a2c5227 Czech Republic (CZ) ebbcdac6-d783-4ef6-aec2-bb6cd4eb5d4b Poland (PL) 9c4145ac-9701-42eb-a9b7-96a1bda4642c Netherlands (NL) 34979ea6-1d69-42bb-9f04-d92e604756b5 Netherlands (NL) 601eb18e-71f9-4bab-97a2-d671fb148cd7 Estonia (EE) fc2c0b97-494f-4a2b-aa3d-066f3304fca2 Greece (GR) 90e38c19-0883-4c5d-8120-cba054768065 Portugal (PT) 5b8264e6-3628-41f1-a0a8-ba6d837e0f5a Bulgaria (BG) f8372a36-bb14-4f2e-81c8-3180ab69367c Sweden (SE) 341ca2ee-895e-4563-b591-272733f2f06b France (FR) 0ab4f341-db89-41d2-8f72-8d45b8421388 Sweden (SE) 7eba0fb8-cd03-4e10-a726-06883cfc36b4 Poland (PL) 380e1957-1bbb-40f2-aa62-e2c21ca3fee5 Germany (DE) 1b37528a-776b-46b9-bea8-5ee1c305a03b Germany (DE)

Technical

Input Voltage (U_{in})	230 V
Input Voltage Type	AC
Rated Frequency (f)	Primary 50 Hz Primary 60 Hz Secondary 50 Hz Secondary 60 Hz
Apparent Power Output	800 V·A
Rated Output Power	480 W
Communication Interface	USB, RS-232
Number of Phases	Primary - 1 Secondary - 1
Number of Outputs	C13 Connection 4
Connection Type	IEC C14
Display Type	LCD
Options Provided	Auto shut down function
Battery Chemical Composition	Lead-Acid

Battery Type	Portable
Battery Weight	2.5 kg
Number of Batteries	1

Dimensions

Product Net Width	122 mm
Product Net Height	160 mm
Product Net Depth / Length	315 mm
Product Net Weight	4.7 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	197 mm
Package Level 1 Height	250 mm
Package Level 1 Depth / Length	395 mm
Package Level 1 Gross Weight	6 kg
Package Level 1 EAN	7640169262616

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044000
Country of Origin	China (CN)

Certificates and Declarations

Declaration of Conformity - CCC	No certification needed
Declaration of Conformity - CE	4NWD004317

Popular Downloads

Data Sheet, Technical Information	4NWD004445_ML
Instructions and Manuals	4NWD004445_ML
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658

Classifications

ETIM 7	EC000382 - UPS
ETIM 8	EC000382 - UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000
eClass	V11.1 : 27040690

Object Classification Code

G

Categories

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 LI IEC 230V

