

PRODUCT-DETAILS

# UPS PowerValue 11LI Up 1000 VA

## UPS PowerValue 11LI Up 1000 VA



### General Information

Extended Product Type	UPS PowerValue 11LI Up 1000 VA
Product ID	4NWP100172R0001
EAN	7640169262623
Catalog Description	UPS PowerValue 11LI Up 1000 VA
Long Description	VI UPS PowerValue 11LI Up 1000VA/600W;230V;50/60Hz;simulated sinewave;3 min

### Circular Value

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD004620
RoHS Information	4NWD004317
SCIP	ea68414c-d4fb-433b-ba08-4a03c1614670 Switzerland (CH)
Simplified SCIP	1cf08ede-f99d-48f5-82e7-6eb5c103825d Czech Republic (CZ) 48c997c9-2bda-4851-a61e-2569006b9ea9 Poland (PL) e8e5abd5-c46a-4c31-a88c-a6965b271915 Netherlands (NL) f178479b-2f07-47b8-9573-8b057e0425da Netherlands (NL) ff30f193-b61f-4250-a471-e883785efe0a Germany (DE) 13fd1aa1-b6c3-4ae4-ae65-dca4d28c1a93 Denmark (DK) b51a002d-8f0f-405c-8dee-bf8776524277 Poland (PL) d650f526-3faf-4c06-9c2e-840f832ecd23 Norway (NO) e21bc697-77bb-4863-8df9-494ebae2a596 Finland (FI) e7c6b406-b451-4753-b2d6-c8408e9ffa73 Netherlands (NL) 4617a0de-5f2d-468e-9303-2fc8957ed5f9 Germany (DE) 6f92732b-3eb7-4c54-aec0-4598e126703e Croatia (HR)

991e409f-4791-46bf-aaa4-63d0236045a3 Poland (PL)  
 1683c4fd-2f72-4387-9477-b874c926b147 Germany (DE)  
 795c06db-3c22-4804-955e-a325edacaf92 Germany (DE)  
 79d4b102-3145-4e87-8ad6-9929c2a02237 France (FR)  
 05b15f8c-0ed4-4777-85a9-794aa166cbc8 Netherlands (NL)  
 361649d8-f616-4315-bbb0-b2f8cf7c3b1d Spain (ES)  
 6c9074e3-240b-4028-99e2-33d69a3b6180 Netherlands (NL)  
 11e855a2-f858-415e-bd31-3d66fafa5b4f Estonia (EE)  
 8be49968-68cc-4066-8624-97c1e6f190bb Greece (GR)  
 5f28e5b4-6e34-48d4-bebd-84638224bce0 Portugal (PT)  
 13ac629f-e65b-487a-8515-394fa47b5259 Bulgaria (BG)  
 372793f0-0694-41aa-8e76-4804a26aac51 Sweden (SE)  
 d24a5b00-6b48-4873-9dca-90f372f1380b France (FR)  
 9ef7587c-95f9-4cb2-a638-cc33caa21c3c Sweden (SE)

## Environmental

Ambient Air Temperature	Storage -15...+60 °C
RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	No declaration needed
SCIP	ea68414c-d4fb-433b-ba08-4a03c1614670 Switzerland (CH)
Simplified SCIP	1cf08ede-f99d-48f5-82e7-6eb5c103825d Czech Republic (CZ) 48c997c9-2bda-4851-a61e-2569006b9ea9 Poland (PL) e8e5abd5-c46a-4c31-a88c-a6965b271915 Netherlands (NL) f178479b-2f07-47b8-9573-8b057e0425da Netherlands (NL) ff30f193-b61f-4250-a471-e883785efe0a Germany (DE) 13fd1aa1-b6c3-4ae4-ae65-dca4d28c1a93 Denmark (DK) b51a002d-8f0f-405c-8dee-bf8776524277 Poland (PL) d650f526-3faf-4c06-9c2e-840f832ecd23 Norway (NO) e21bc697-77bb-4863-8df9-494ebae2a596 Finland (FI) e7c6b406-b451-4753-b2d6-c8408e9ffa73 Netherlands (NL) 4617a0de-5f2d-468e-9303-2fc8957ed5f9 Germany (DE) 6f92732b-3eb7-4c54-aec0-4598e126703e Croatia (HR) 991e409f-4791-46bf-aaa4-63d0236045a3 Poland (PL) 1683c4fd-2f72-4387-9477-b874c926b147 Germany (DE) 795c06db-3c22-4804-955e-a325edacaf92 Germany (DE) 79d4b102-3145-4e87-8ad6-9929c2a02237 France (FR) 05b15f8c-0ed4-4777-85a9-794aa166cbc8 Netherlands (NL) 361649d8-f616-4315-bbb0-b2f8cf7c3b1d Spain (ES) 6c9074e3-240b-4028-99e2-33d69a3b6180 Netherlands (NL) 11e855a2-f858-415e-bd31-3d66fafa5b4f Estonia (EE) 8be49968-68cc-4066-8624-97c1e6f190bb Greece (GR) 5f28e5b4-6e34-48d4-bebd-84638224bce0 Portugal (PT) 13ac629f-e65b-487a-8515-394fa47b5259 Bulgaria (BG) 372793f0-0694-41aa-8e76-4804a26aac51 Sweden (SE) d24a5b00-6b48-4873-9dca-90f372f1380b France (FR) 9ef7587c-95f9-4cb2-a638-cc33caa21c3c Sweden (SE)

## Technical

Input Voltage ( $U_{in}$ )	230 V
Input Voltage Type	AC
Rated Frequency (f)	Primary 50 Hz Primary 60 Hz Secondary 50 Hz Secondary 60 Hz
Apparent Power Output	1000 V·A
Rated Output Power	600 W
Communication Interface	USB, RS-232
Number of Phases	Primary - 1 Secondary - 1
Number of Outputs	C13 Connection 6
Connection Type	IEC C14
Display Type	LCD
Options Provided	Auto shut down function
Battery Chemical Composition	Lead-Acid

Battery Type	Portable
Battery Weight	2.1 kg
Number of Batteries	2

## Dimensions

Product Net Width	145 mm
Product Net Height	190 mm
Product Net Depth / Length	335 mm
Product Net Weight	7.5 kg

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	228 mm
Package Level 1 Height	287 mm
Package Level 1 Depth / Length	410 mm
Package Level 1 Gross Weight	10 kg
Package Level 1 EAN	7640169262623

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044000
Country of Origin	China (CN)

## Certificates and Declarations

Declaration of Conformity - CCC	No certification needed
Declaration of Conformity - CE	4NWD004317

## Popular Downloads

Data Sheet, Technical Information	4NWD004445_ML
Instructions and Manuals	4NWD004445_ML
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658

## Classifications

ETIM 7	EC000382 - UPS
ETIM 8	EC000382 - UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000
eClass	V11.1 : 27040690

---

Object Classification Code

G

---

## Categories

---

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 LI IEC 230V

