

PRODUCT-DETAILS

# UPS PowerValue 11LI Up 1500 VA

# UPS PowerValue 11LI Up 1500 VA



## General Information

Extended Product Type	UPS PowerValue 11LI Up 1500 VA
Product ID	4NWP100173R0001
EAN	7640169262630
Catalog Description	UPS PowerValue 11LI Up 1500 VA
Long Description	VI UPS PowerValue 11LI Up 1500VA/900W;230V;50/60Hz;simulated sinewave;4 min

## Circular Value

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD004620
RoHS Information	4NWD004317
SCIP	c4c92015-4bfc-4971-85b7-c47760a1fe7b Switzerland (CH)
Simplified SCIP	7ba2fbbc-98ae-4f8a-b2f4-d738f796d2b0 Estonia (EE) 580edc03-9c26-4d99-b329-41acf38d2d9d Greece (GR) f443f5ef-c5a5-4d1b-8657-8dcebb408a7c Portugal (PT) 20e42b59-d201-460d-afaf-122bdb2feb41 Bulgaria (BG) 690a2342-4ebe-4b24-9f29-9f1c30be480d Sweden (SE) 35f8b6f3-689e-46a0-9de4-68d3424dfe54 France (FR) caed7a7c-d54d-4e1e-9c16-75a2c43c2972 Sweden (SE) 373bec92-2fd8-48be-9834-3c71fe4014d4 Poland (PL)

7d6f88c2-d2ba-4897-9307-c11e6f8fe96e Germany (DE)  
 8cd648c1-c725-4db3-b240-734991e9fa03 Germany (DE)  
 a859e988-fe9c-4605-9bee-2eeb7b30ee78 France (FR)  
 4903e804-d01f-4e18-b1bd-e42937611761 Netherlands (NL)  
 ad1bafa8-3f8f-46ba-9f6d-a0890c79307f Spain (ES)  
 4b94a620-1d9c-47dd-be8a-9311bd63fea4 Netherlands (NL)  
 95260678-5f19-465f-957b-12d3deb82315 Germany (DE)  
 fbacc13f-cb51-4665-896d-a3a0c3dfb74b Denmark (DK)  
 a1607da1-6b21-493d-8d51-415147d63244 Poland (PL)  
 7344addb-bbb6-41a2-8b96-3039178d7df2 Norway (NO)  
 5f90a988-9654-4b38-83da-51283b024c93 Finland (FI)  
 2c2f8250-fb44-4a2c-ba08-f50104f7147c Netherlands (NL)  
 4684002b-325a-414d-83c2-0dd974301d89 Germany (DE)  
 5fbd6f99-a1f5-47f3-ac90-2b4f628d501f Croatia (HR)  
 3da30851-29cb-4ca6-8b02-7c2cc16f6460 Czech Republic (CZ)  
 a690df28-7ace-43bc-b638-2236677d738a Poland (PL)  
 240cc719-0bd5-4b6a-9820-8b07a4edd4de Netherlands (NL)  
 ed600d36-6e08-46e4-b439-6e543e4f7843 Netherlands (NL)

## Environmental

Ambient Air Temperature	Storage -15...+60 °C
RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	No declaration needed
SCIP	c4c92015-4bfc-4971-85b7-c47760a1fe7b Switzerland (CH)
Simplified SCIP	7ba2fbbc-98ae-4f8a-b2f4-d738f796d2b0 Estonia (EE) 580edc03-9c26-4d99-b329-41acf38d2d9d Greece (GR) f443f5ef-c5a5-4d1b-8657-8dcebb408a7c Portugal (PT) 20e42b59-d201-460d-afaf-122bdb2feb41 Bulgaria (BG) 690a2342-4ebe-4b24-9f29-9f1c30be480d Sweden (SE) 35f8b6f3-689e-46a0-9de4-68d3424dfe54 France (FR) caed7a7c-d54d-4e1e-9c16-75a2c43c2972 Sweden (SE) 373bec92-2fd8-48be-9834-3c71fe4014d4 Poland (PL) 7d6f88c2-d2ba-4897-9307-c11e6f8fe96e Germany (DE) 8cd648c1-c725-4db3-b240-734991e9fa03 Germany (DE) a859e988-fe9c-4605-9bee-2eeb7b30ee78 France (FR) 4903e804-d01f-4e18-b1bd-e42937611761 Netherlands (NL) ad1bafa8-3f8f-46ba-9f6d-a0890c79307f Spain (ES) 4b94a620-1d9c-47dd-be8a-9311bd63fea4 Netherlands (NL) 95260678-5f19-465f-957b-12d3deb82315 Germany (DE) fbacc13f-cb51-4665-896d-a3a0c3dfb74b Denmark (DK) a1607da1-6b21-493d-8d51-415147d63244 Poland (PL) 7344addb-bbb6-41a2-8b96-3039178d7df2 Norway (NO) 5f90a988-9654-4b38-83da-51283b024c93 Finland (FI) 2c2f8250-fb44-4a2c-ba08-f50104f7147c Netherlands (NL) 4684002b-325a-414d-83c2-0dd974301d89 Germany (DE) 5fbd6f99-a1f5-47f3-ac90-2b4f628d501f Croatia (HR) 3da30851-29cb-4ca6-8b02-7c2cc16f6460 Czech Republic (CZ) a690df28-7ace-43bc-b638-2236677d738a Poland (PL) 240cc719-0bd5-4b6a-9820-8b07a4edd4de Netherlands (NL) ed600d36-6e08-46e4-b439-6e543e4f7843 Netherlands (NL)

## Technical

Input Voltage ( $U_{in}$ )	230 V
Input Voltage Type	AC
Rated Frequency (f)	Primary 50 Hz Primary 60 Hz Secondary 50 Hz Secondary 60 Hz
Apparent Power Output	1500 V·A

Rated Output Power	900 W
Communication Interface	USB, RS-232
Number of Phases	Primary - 1 Secondary - 1
Number of Outputs	C13 Connection 6
Connection Type	IEC C14
Display Type	LCD
Options Provided	Auto shut down function
Battery Chemical Composition	Lead-Acid
Battery Type	Portable
Battery Weight	2.5 kg
Number of Batteries	2

## Dimensions

Product Net Width	145 mm
Product Net Height	190 mm
Product Net Depth / Length	335 mm
Product Net Weight	9.8 kg

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	228 mm
Package Level 1 Height	287 mm
Package Level 1 Depth / Length	410 mm
Package Level 1 Gross Weight	12 kg
Package Level 1 EAN	7640169262630

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044000
Country of Origin	China (CN)

## Certificates and Declarations

Declaration of Conformity - CCC	No certification needed
Declaration of Conformity - CE	4NWD004317

## Popular Downloads

Data Sheet, Technical Information	4NWD004445_ML
Instructions and Manuals	4NWD004445_ML
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658

## Classifications

ETIM 7	EC000382 - UPS
ETIM 8	EC000382 - UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000
eClass	V11.1 : 27040690
Object Classification Code	G

## Categories

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 LI IEC 230V

