

PRODUCT-DETAILS

# UPS PowerValue 11LI Up 2000 VA

## UPS PowerValue 11LI Up 2000 VA



### General Information

Extended Product Type	UPS PowerValue 11LI Up 2000 VA
Product ID	4NWP100174R0001
EAN	7640169262647
Catalog Description	UPS PowerValue 11LI Up 2000 VA
Long Description	VI UPS PowerValue 11LI Up 2000VA/1200W;230V;50/60Hz;simulated sinewave;2.5 min

### Circular Value

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD004620
RoHS Information	4NWD004317
SCIP	ef6317aa-8ab5-43d2-b06e-9898a8008c30 Switzerland (CH)
Simplified SCIP	00043cca-ac63-495f-bef0-f8b1f9f232d9 Netherlands (NL) 3ca81253-042f-404a-bea9-88fa4d1174a5 Poland (PL) 1e1e85b4-fbaa-46e8-9dbb-5d4d43b6addd Netherlands (NL) ee243792-af91-4dde-9443-26541c5e8049 Netherlands (NL) 50476235-3130-4fa3-b331-59784baebaea Estonia (EE) 0e676254-50ef-4726-beae-550c892952c0 Greece (GR) 1ed45473-4f88-4c3d-8451-91b68bf012e1 Portugal (PT) a1cb1455-7d73-46ad-934a-2f15feee9149 Bulgaria (BG) 98ed12e1-cf0d-4ae7-b668-b15b6adfc271 Sweden (SE) ffa49d11-bf98-40e3-a0c2-a86b2f524499 France (FR) b9fc1b64-dbf0-4613-8923-9e9ae71ff741 Sweden (SE) 7dec86a8-891f-4fde-8bf3-485d2c09032c Poland (PL)

a4d5a73e-cd98-4a54-9660-95135b4e5f65 Germany (DE)  
 8b2dbeb0-864b-41ff-ae9f-11d0b2ba471d Germany (DE)  
 6bcf30fe-4a35-438a-82c5-d4e879ff59fa France (FR)  
 b72d2200-6dc3-4ab3-8b9f-41bb8a4c2d6b Netherlands (NL)  
 08756326-7ab2-4002-bda5-4f2b69f1ad6f Spain (ES)  
 6a44bdae-c8d0-41ef-b3b9-f2bb643879be Germany (DE)  
 4970bf50-6fca-44b2-ba94-ee42848e9a2e Denmark (DK)  
 1860834e-8465-410c-8edb-28ecfb3caff5 Poland (PL)  
 f95d3b35-81a5-4da0-a5da-9b807a4afb6e Norway (NO)  
 4f3cab6f-a823-4d34-9121-3e0938a7164b Finland (FI)  
 6ee3f992-59c9-41b3-9ca2-5655799f5516 Netherlands (NL)  
 620d4f24-1c23-47e7-abea-1d50fe43a15d Germany (DE)  
 bb06679d-ec14-401b-b952-12407aa9da54 Croatia (HR)  
 e3707150-4520-4e80-a722-99f6416ac47e Czech Republic (CZ)

## Environmental

Ambient Air Temperature	Storage -15...+60 °C
RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	No declaration needed
SCIP	ef6317aa-8ab5-43d2-b06e-9898a8008c30 Switzerland (CH)
Simplified SCIP	00043cca-ac63-495f-bef0-f8b1f9f232d9 Netherlands (NL) 3ca81253-042f-404a-bea9-88fa4d1174a5 Poland (PL) 1e1e85b4-fbaa-46e8-9dbb-5d4d43b6addd Netherlands (NL) ee243792-af91-4dde-9443-26541c5e8049 Netherlands (NL) 50476235-3130-4fa3-b331-59784baebaea Estonia (EE) 0e676254-50ef-4726-beae-550c892952c0 Greece (GR) 1ed45473-4f88-4c3d-8451-91b68bf012e1 Portugal (PT) a1cb1455-7d73-46ad-934a-2f15feee9149 Bulgaria (BG) 98ed12e1-cf0d-4ae7-b668-b15b6adfc271 Sweden (SE) ffa49d11-bf98-40e3-a0c2-a86b2f524499 France (FR) b9fc1b64-dbf0-4613-8923-9e9ae71ff741 Sweden (SE) 7dec86a8-891f-4fde-8bf3-485d2c09032c Poland (PL) a4d5a73e-cd98-4a54-9660-95135b4e5f65 Germany (DE) 8b2dbeb0-864b-41ff-ae9f-11d0b2ba471d Germany (DE) 6bcf30fe-4a35-438a-82c5-d4e879ff59fa France (FR) b72d2200-6dc3-4ab3-8b9f-41bb8a4c2d6b Netherlands (NL) 08756326-7ab2-4002-bda5-4f2b69f1ad6f Spain (ES) 6a44bdae-c8d0-41ef-b3b9-f2bb643879be Germany (DE) 4970bf50-6fca-44b2-ba94-ee42848e9a2e Denmark (DK) 1860834e-8465-410c-8edb-28ecfb3caff5 Poland (PL) f95d3b35-81a5-4da0-a5da-9b807a4afb6e Norway (NO) 4f3cab6f-a823-4d34-9121-3e0938a7164b Finland (FI) 6ee3f992-59c9-41b3-9ca2-5655799f5516 Netherlands (NL) 620d4f24-1c23-47e7-abea-1d50fe43a15d Germany (DE) bb06679d-ec14-401b-b952-12407aa9da54 Croatia (HR) e3707150-4520-4e80-a722-99f6416ac47e Czech Republic (CZ)

## Technical

Input Voltage ( $U_{in}$ )	230 V
Input Voltage Type	AC
Rated Frequency (f)	Primary 50 Hz Primary 60 Hz Secondary 50 Hz Secondary 60 Hz
Apparent Power Output	2000 V·A
Rated Output Power	1200 W
Communication Interface	USB, RS-232
Number of Phases	Primary - 1 Secondary - 1
Number of Outputs	C13 Connection 6
Connection Type	IEC C14
Display Type	LCD
Options Provided	Auto shut down function
Battery Chemical Composition	Lead-Acid

Battery Type	Portable
Battery Weight	2.5 kg
Number of Batteries	2

## Dimensions

Product Net Width	145 mm
Product Net Height	190 mm
Product Net Depth / Length	335 mm
Product Net Weight	10.7 kg

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	228 mm
Package Level 1 Height	287 mm
Package Level 1 Depth / Length	410 mm
Package Level 1 Gross Weight	13 kg
Package Level 1 EAN	7640169262647

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044000
Country of Origin	China (CN)

## Certificates and Declarations

Declaration of Conformity - CCC	No certification needed
Declaration of Conformity - CE	4NWD004317

## Popular Downloads

Data Sheet, Technical Information	4NWD004445_ML
Instructions and Manuals	4NWD004445_ML
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658

## Classifications

ETIM 7	EC000382 - UPS
ETIM 8	EC000382 - UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000
eClass	V11.1 : 27040690

---

Object Classification Code

G

---

## Categories

---

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 LI IEC 230V

