

PRODUCT-DETAILS

UPS PowerValue 11LI Pro 600 VA

UPS PowerValue 11LI Pro 600 VA



General Information

Extended Product Type	UPS PowerValue 11LI Pro 600 VA
Product ID	4NWP100175R0001
EAN	7640169262654
Catalog Description	UPS PowerValue 11LI Pro 600 VA
Long Description	VI UPS PowerValue 11LI Pro 600VA/360W;230V;50/60Hz;pure sinewave;3.5 min

Circular Value

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD004620
RoHS Information	4NWD004322
SCIP	866b8e18-e55e-4ac7-b987-f09b84de7d2c Switzerland (CH)
Simplified SCIP	9169fbcd-d534-47a5-8214-42fa1b12850b Germany (DE) a888b95a-8a95-48ba-8c30-c7964028ec70 Poland (PL) 04280b63-c3b7-4cf6-8afe-e5b143b5bbe7 Norway (NO) 865ce31e-100b-4f6a-8174-0a9744331148 Finland (FI) b21cf44c-45c2-409d-839c-1df4dec59103 Netherlands (NL) 442cfee5-fa4f-4cd7-b4ce-61d997be15ff Germany (DE) 86cf6aae-4f46-4eba-a7e0-b093172d43d1 Croatia (HR) cca08529-0466-4c7a-a57e-60c7f93d4c8c Denmark (DK) aff6b0da-7db4-40b1-a10e-467b76135e88 Czech Republic (CZ) e8553b35-de11-4780-9783-9fa9d827e158 Poland (PL) 165a16dc-32cf-4f82-85cc-b35f7e9e103e Netherlands (NL) 9e1a2180-2e40-4dc7-bb8f-58481f2cfa6e Netherlands (NL)

7bf02fc3-7cc4-4708-be62-b7003af69a9f Estonia (EE)
 8cfa4309-5f57-4ea0-8cdf-eed1339d3f53 Germany (DE)
 f402ee94-75ad-4aba-baf8-b745b35350f5 Germany (DE)
 68f8974a-ec83-45d7-98db-71bd36090e41 France (FR)
 13accc49-9426-4249-9b63-3406ddb5bef Netherlands (NL)
 5f87c2ac-4e35-450d-bc0c-85cde638dd1a Spain (ES)
 38e7dfc2-7e65-4d92-be6a-646968d85111 Netherlands (NL)
 e5f43a95-493f-4b8c-bef8-233f7c2e70ee Greece (GR)
 91e89977-d78a-4b44-9adc-08a8cae2aeef Portugal (PT)
 748737ca-d624-473c-a37a-231cac6068a9 Bulgaria (BG)
 90620e8a-55a8-45d2-946b-250900dffb96 Sweden (SE)
 cd017728-7bf4-4acf-89a4-82bb08782976 France (FR)
 1e55adb4-50b5-4fc9-bc66-edd5b2a65037 Sweden (SE)
 b9d04015-2da6-4fbc-a81b-feb75f7d3d12 Poland (PL)

Environmental

Ambient Air Temperature	Storage -15...+60 °C
RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	No declaration needed
SCIP	866b8e18-e55e-4ac7-b987-f09b84de7d2c Switzerland (CH)
Simplified SCIP	9169fbc-d534-47a5-8214-42fa1b12850b Germany (DE) a888b95a-8a95-48ba-8c30-c7964028ec70 Poland (PL) 04280b63-c3b7-4cf6-8afe-e5b143b5bbe7 Norway (NO) 865ce31e-100b-4f6a-8174-0a9744331148 Finland (FI) b21cf44c-45c2-409d-839c-1df4dec59103 Netherlands (NL) 442cfee5-fa4f-4cd7-b4ce-61d997be15ff Germany (DE) 86cf6aae-4f46-4eba-a7e0-b093172d43d1 Croatia (HR) cca08529-0466-4c7a-a57e-60c7f93d4c8c Denmark (DK) aff6b0da-7db4-40b1-a10e-467b76135e88 Czech Republic (CZ) e8553b35-de11-4780-9783-9fa9d827e158 Poland (PL) 165a16dc-32cf-4f82-85cc-b35f7e9e103e Netherlands (NL) 9e1a2180-2e40-4dc7-bb8f-58481f2cfa6e Netherlands (NL) 7bf02fc3-7cc4-4708-be62-b7003af69a9f Estonia (EE) 8cfa4309-5f57-4ea0-8cdf-eed1339d3f53 Germany (DE) f402ee94-75ad-4aba-baf8-b745b35350f5 Germany (DE) 68f8974a-ec83-45d7-98db-71bd36090e41 France (FR) 13accc49-9426-4249-9b63-3406ddb5bef Netherlands (NL) 5f87c2ac-4e35-450d-bc0c-85cde638dd1a Spain (ES) 38e7dfc2-7e65-4d92-be6a-646968d85111 Netherlands (NL) e5f43a95-493f-4b8c-bef8-233f7c2e70ee Greece (GR) 91e89977-d78a-4b44-9adc-08a8cae2aeef Portugal (PT) 748737ca-d624-473c-a37a-231cac6068a9 Bulgaria (BG) 90620e8a-55a8-45d2-946b-250900dffb96 Sweden (SE) cd017728-7bf4-4acf-89a4-82bb08782976 France (FR) 1e55adb4-50b5-4fc9-bc66-edd5b2a65037 Sweden (SE) b9d04015-2da6-4fbc-a81b-feb75f7d3d12 Poland (PL)

Technical

Input Voltage (U _{in})	230 V
Input Voltage Type	AC
Rated Frequency (f)	Primary 50 Hz Primary 60 Hz Secondary 50 Hz Secondary 60 Hz
Apparent Power Output	600 V·A
Rated Output Power	360 W
Communication Interface	USB, RS-232
Number of Phases	Primary - 1 Secondary - 1
Number of Outputs	C13 Connection 4
Connection Type	IEC C14
Display Type	LCD
Options Provided	Auto shut down function
Battery Chemical Composition	Lead-Acid

Battery Type	Portable
Battery Weight	2.1 kg
Number of Batteries	1

Dimensions

Product Net Width	100 mm
Product Net Height	145 mm
Product Net Depth / Length	328 mm
Product Net Weight	6 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	140 mm
Package Level 1 Height	228 mm
Package Level 1 Depth / Length	385 mm
Package Level 1 Gross Weight	7.2 kg
Package Level 1 EAN	7640169262654

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044000
E-Number (Finland)	8408629
Country of Origin	China (CN)

Certificates and Declarations

Declaration of Conformity - CCC	No certification needed
Declaration of Conformity - CE	4NWD004322

Popular Downloads

Data Sheet, Technical Information	4NWD004444_ML
Instructions and Manuals	4NWD004444_ML
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658

Classifications

ETIM 7	EC000382 - UPS
ETIM 8	EC000382 - UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000

eClass	V11.1 : 27040690
Object Classification Code	G

Categories

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 LI IEC 230V

