

PRODUCT-DETAILS

UPS PowerValue 11LI Pro 800 VA

UPS PowerValue 11LI Pro 800 VA



General Information

Extended Product Type	UPS PowerValue 11LI Pro 800 VA
Product ID	4NWP100176R0001
EAN	7640169262661
Catalog Description	UPS PowerValue 11LI Pro 800 VA
Long Description	VI UPS PowerValue 11LI Pro 800VA/480W;230V;50/60Hz;pure sinewave;2.5 min

Circular Value

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD004620
RoHS Information	4NWD004322
SCIP	424cab99-027a-4c83-bed6-c736eef883ff Switzerland (CH)
Simplified SCIP	bdaefabb-71cd-44b1-96f1-ecfa49f3ff34 Netherlands (NL) a06a9ce3-b60f-4ade-87ce-65956b949e95 Germany (DE) f30e2997-56e2-4141-8774-7f7165ea6bb6 Croatia (HR) abe0cc33-793b-4193-a3d4-e3ebf5e8a55b Denmark (DK) f06baa1b-34f7-4b14-850f-9c0bb7956c1c Czech Republic (CZ) f490c704-346f-43b0-8503-8cd628116384 Poland (PL) 4f94c215-4216-4958-98d6-c044cde00f3f Netherlands (NL) be5788d1-b127-460f-b65b-7c0312edc67b Netherlands (NL) cda211ec-8567-44f1-89fb-3cf62bc53d52 Estonia (EE) 5e91bd56-1daf-4da9-a3e8-02d473423479 Greece (GR) 3475bbec-c17a-46a7-bb5f-6fcd4777e1b0 Portugal (PT) 59ad7310-57ad-44d8-8ef3-aff4e4ee8c42 Bulgaria (BG)

efd9abcd-406e-4557-b2bf-76e4a5a7c5bb Sweden (SE)
 240c340d-5811-4f0c-a440-de77baa0a00f France (FR)
 697fe351-1c70-49f7-acdb-4823ebdb16a0 Sweden (SE)
 3895262b-0480-4244-89e2-26c731cdd1a8 Poland (PL)
 acaf8901-1982-43d4-9d17-2269d2c5175e Germany (DE)
 5b3f2b17-8ca5-4894-be26-8dbc02fee7d Germany (DE)
 537f45e4-b9a8-4572-a9fb-3468afec4eaa France (FR)
 a6f4e02b-97ca-4dc6-860a-65844f5f0154 Netherlands (NL)
 72061038-c282-4ea6-bb32-d7405f57a3f1 Spain (ES)
 570930bb-88c7-4e02-99b1-1e552da09640 Germany (DE)
 ad7b2971-75a4-4e59-94ff-13925fabf230 Poland (PL)
 0cfc0132-8efa-4475-a472-272544e7443e Norway (NO)
 057e83c8-aa62-486c-a8d6-11a901005545 Finland (FI)
 e6ab87b1-ecab-476c-a5fe-3486a0147b7a Netherlands (NL)

Environmental

Ambient Air Temperature	Storage -15...+60 °C
RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	No declaration needed
SCIP	424cab99-027a-4c83-bed6-c736eef883ff Switzerland (CH)
Simplified SCIP	bdaefabb-71cd-44b1-96f1-ecfa49f3ff34 Netherlands (NL) a06a9ce3-b60f-4ade-87ce-65956b949e95 Germany (DE) f30e2997-56e2-4141-8774-7f7165ea6bb6 Croatia (HR) abe0cc33-793b-4193-a3d4-e3ebf5e8a55b Denmark (DK) f06baa1b-34f7-4b14-850f-9c0bb7956c1c Czech Republic (CZ) f490c704-346f-43b0-8503-8cd628116384 Poland (PL) 4f94c215-4216-4958-98d6-c044cde00f3f Netherlands (NL) be5788d1-b127-460f-b65b-7c0312edc67b Netherlands (NL) cda211ec-8567-44f1-89fb-3cf62bc53d52 Estonia (EE) 5e91bd56-1daf-4da9-a3e8-02d473423479 Greece (GR) 3475bbee-c17a-46a7-bb5f-6fcd777e1b0 Portugal (PT) 59ad7310-57ad-44d8-8ef3-aff4e4ee8c42 Bulgaria (BG) efd9abcd-406e-4557-b2bf-76e4a5a7c5bb Sweden (SE) 240c340d-5811-4f0c-a440-de77baa0a00f France (FR) 697fe351-1c70-49f7-acdb-4823ebdb16a0 Sweden (SE) 3895262b-0480-4244-89e2-26c731cdd1a8 Poland (PL) acaf8901-1982-43d4-9d17-2269d2c5175e Germany (DE) 5b3f2b17-8ca5-4894-be26-8dbc02fee7d Germany (DE) 537f45e4-b9a8-4572-a9fb-3468afec4eaa France (FR) a6f4e02b-97ca-4dc6-860a-65844f5f0154 Netherlands (NL) 72061038-c282-4ea6-bb32-d7405f57a3f1 Spain (ES) 570930bb-88c7-4e02-99b1-1e552da09640 Germany (DE) ad7b2971-75a4-4e59-94ff-13925fabf230 Poland (PL) 0cfc0132-8efa-4475-a472-272544e7443e Norway (NO) 057e83c8-aa62-486c-a8d6-11a901005545 Finland (FI) e6ab87b1-ecab-476c-a5fe-3486a0147b7a Netherlands (NL)

Technical

Input Voltage (U _{in})	230 V
Input Voltage Type	AC
Rated Frequency (f)	Primary 50 Hz Primary 60 Hz Secondary 50 Hz Secondary 60 Hz
Apparent Power Output	800 V·A
Rated Output Power	480 W
Communication Interface	USB, RS-232
Number of Phases	Primary - 1 Secondary - 1
Number of Outputs	C13 Connection 4
Connection Type	IEC C14
Display Type	LCD
Options Provided	Auto shut down function
Battery Chemical Composition	Lead-Acid

Battery Type	Portable
Battery Weight	2.5 kg
Number of Batteries	1

Dimensions

Product Net Width	10 mm
Product Net Height	145 mm
Product Net Depth / Length	328 mm
Product Net Weight	6.6 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	140 mm
Package Level 1 Height	228 mm
Package Level 1 Depth / Length	385 mm
Package Level 1 Gross Weight	7.9 kg
Package Level 1 EAN	7640169262661

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044000
E-Number (Finland)	8408630
Country of Origin	China (CN)

Certificates and Declarations

Declaration of Conformity - CCC	No certification needed
Declaration of Conformity - CE	4NWD004322

Popular Downloads

Data Sheet, Technical Information	4NWD004444_ML
Instructions and Manuals	4NWD004444_ML
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658

Classifications

ETIM 7	EC000382 - UPS
ETIM 8	EC000382 - UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000

eClass	V11.1 : 27040690
Object Classification Code	G

Categories

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 LI IEC 230V

