

PRODUCT-DETAILS

# UPS PowerValue 11LI Pro 1000 VA

# UPS PowerValue 11LI Pro 1000 VA



## General Information

Extended Product Type	UPS PowerValue 11LI Pro 1000 VA
Product ID	4NWP100177R0001
EAN	7640169262678
Catalog Description	UPS PowerValue 11LI Pro 1000 VA
Long Description	VI UPS PowerValue 11LI Pro 1000VA/700W;230V;50/60Hz;pure sinewave;6 min

## Circular Value

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD004620
RoHS Information	4NWD004322
SCIP	cc1c2097-a9b0-4b46-9ebb-565f3d0fceb7 Switzerland (CH)
Simplified SCIP	7e920fc2-4c85-4e33-88e0-392bd2f7e9c5 Germany (DE) f0fa8059-4b24-4fc3-acd6-b55a081eb083 Poland (PL) 54501ec4-bb78-409f-ad17-15a38929372c Norway (NO) b7af7b6c-c35a-47bf-a627-29d04b33bfe1 Finland (FI) a1ca1eb7-a326-482f-9325-ba2fe6b0ce0b Netherlands (NL) 0dbdd6b7-bbe7-4a34-bbb7-7359d97c80fd Germany (DE) 9089dd0c-b118-43cf-9810-54ff2181fdf1 Denmark (DK) ef3b7ac0-edad-4d76-95e2-42a32fcd30d Croatia (HR) 3a485796-e78a-4edb-b60e-3cfac2c1b265 Czech Republic (CZ) 7d6f97fa-f16e-4d5f-b103-8d57810e5119 Poland (PL) 260f1297-852f-4e9f-9500-8a0ec4a62d5c Netherlands (NL) d8b99f6b-ae88-4e1d-b488-75a9fb061b7b Netherlands (NL)

bf9ff087-da13-4e26-8b1e-8579d9b365bd Estonia (EE)  
 5cdd0e75-0bc5-489d-a953-7636c6370a5e Greece (GR)  
 95c47c5e-c8a5-4172-8787-b708532a0eee Portugal (PT)  
 48951e9e-3a8d-4173-8121-14ce2032851a Bulgaria (BG)  
 243bfa15-2e6c-4853-8ad5-0a8968e84108 Sweden (SE)  
 5c290af9-5be0-4719-a8aa-ae22576df85e France (FR)  
 e32425fb-c0a7-42de-a0dd-e99acfd13263 Poland (PL)  
 3e662b2e-1821-4136-9b7a-097d546ec583 Sweden (SE)  
 dff23696-f5d4-409d-8f60-ab34c2a35315 Germany (DE)  
 b7b0f622-ad43-4c23-b7e5-126976fe2079 Germany (DE)  
 2f65c3a3-483d-4541-9fae-2a12004fa8d8 France (FR)  
 6fc8cd66-bff2-4a55-aff6-7529dde57180 Netherlands (NL)  
 890f26cf-24dc-4df0-ac29-628f6fc00a7f Spain (ES)  
 ae91e210-d3db-49fe-a1e8-077ac9b02ded Netherlands (NL)

**Environmental**

Ambient Air Temperature	Storage -15...+60 °C
RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	No declaration needed
SCIP	cc1c2097-a9b0-4b46-9ebb-565f3d0fceb7 Switzerland (CH)
Simplified SCIP	7e920fc2-4c85-4e33-88e0-392bd2f7e9c5 Germany (DE) f0fa8059-4b24-4fc3-acd6-b55a081eb083 Poland (PL) 54501ec4-bb78-409f-ad17-15a38929372c Norway (NO) b7af7b6c-c35a-47bf-a627-29d04b33bfe1 Finland (FI) a1ca1eb7-a326-482f-9325-ba2fe6b0ce0b Netherlands (NL) 0dbdd6b7-bbe7-4a34-bbb7-7359d97c80fd Germany (DE) 9089dd0c-b118-43cf-9810-54ff2181fdf1 Denmark (DK) ef3b7ac0-edad-4d76-95e2-42a32fcd30d Croatia (HR) 3a485796-e78a-4edb-b60e-3cfac2c1b265 Czech Republic (CZ) 7d6f97fa-f16e-4d5f-b103-8d57810e5119 Poland (PL) 260f1297-852f-4e9f-9500-8a0ec4a62d5c Netherlands (NL) d8b99f6b-ae8-4e1d-b488-75a9fb061b7b Netherlands (NL) bf9ff087-da13-4e26-8b1e-8579d9b365bd Estonia (EE) 5cdd0e75-0bc5-489d-a953-7636c6370a5e Greece (GR) 95c47c5e-c8a5-4172-8787-b708532a0eee Portugal (PT) 48951e9e-3a8d-4173-8121-14ce2032851a Bulgaria (BG) 243bfa15-2e6c-4853-8ad5-0a8968e84108 Sweden (SE) 5c290af9-5be0-4719-a8aa-ae22576df85e France (FR) e32425fb-c0a7-42de-a0dd-e99acfd13263 Poland (PL) 3e662b2e-1821-4136-9b7a-097d546ec583 Sweden (SE) dff23696-f5d4-409d-8f60-ab34c2a35315 Germany (DE) b7b0f622-ad43-4c23-b7e5-126976fe2079 Germany (DE) 2f65c3a3-483d-4541-9fae-2a12004fa8d8 France (FR) 6fc8cd66-bff2-4a55-aff6-7529dde57180 Netherlands (NL) 890f26cf-24dc-4df0-ac29-628f6fc00a7f Spain (ES) ae91e210-d3db-49fe-a1e8-077ac9b02ded Netherlands (NL)

**Technical**

Input Voltage (U <sub>in</sub> )	230 V
Input Voltage Type	AC
Rated Frequency (f)	Primary 50 Hz Primary 60 Hz Secondary 50 Hz Secondary 60 Hz
Apparent Power Output	1000 V·A
Rated Output Power	600 W
Communication Interface	USB, RS-232
Number of Phases	Primary - 1 Secondary - 1
Number of Outputs	C13 Connection 6
Connection Type	IEC C14
Display Type	LCD
Options Provided	Auto shut down function
Battery Chemical Composition	Lead-Acid

Battery Type	Portable
Battery Weight	2.1 kg
Number of Batteries	2

## Dimensions

Product Net Width	146 mm
Product Net Height	205 mm
Product Net Depth / Length	395 mm
Product Net Weight	8 kg

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	236 mm
Package Level 1 Height	297 mm
Package Level 1 Depth / Length	496 mm
Package Level 1 Gross Weight	10.5 kg
Package Level 1 EAN	7640169262678

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044000
E-Number (Finland)	8408631
Country of Origin	China (CN)

## Certificates and Declarations

Declaration of Conformity - CCC	No certification needed
Declaration of Conformity - CE	4NWD004322

## Popular Downloads

Data Sheet, Technical Information	4NWD004444_ML
Instructions and Manuals	4NWD004444_ML
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658

## Classifications

ETIM 7	EC000382 - UPS
ETIM 8	EC000382 - UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000

---

eClass	V11.1 : 27040690
Object Classification Code	G

---

---

## Categories

---

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 LI IEC 230V

