

PRODUCT-DETAILS

# UPS PowerValue 11LI Pro 1500 VA

# UPS PowerValue 11LI Pro 1500 VA



## General Information

Extended Product Type	UPS PowerValue 11LI Pro 1500 VA
Product ID	4NWP100178R0001
EAN	7640169262685
Catalog Description	UPS PowerValue 11LI Pro 1500 VA
Long Description	VI UPS PowerValue 11LI Pro 1500VA/1050W;230V;50/60Hz;pure sinewave;5 min

## Circular Value

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD004620
RoHS Information	4NWD004322
SCIP	f83a26df-8beb-4c54-8294-808bd2c4e276 Switzerland (CH)
Simplified SCIP	<p>0be49677-cc9e-4fc0-8911-f5e8389c541f Germany (DE)</p> <p>a4440343-c230-4a57-b9ba-9a8fa52e5c59 Poland (PL)</p> <p>74e69599-e852-4d23-a06f-0aa85d2d9167 Norway (NO)</p> <p>59cb3396-823b-47ab-b751-83fac10ee147 Finland (FI)</p> <p>2a8ec393-df14-4c7a-a20d-43e5f434a50d Netherlands (NL)</p> <p>436f430c-8f55-4869-a5ca-b26b90e0bbd1 Germany (DE)</p> <p>8ad784ba-0575-4d1d-a283-146baf9c1224 Denmark (DK)</p> <p>cd38ab98-683c-4bba-83d4-5da51343320c Croatia (HR)</p> <p>3437a7e2-88b6-4b36-89c0-d8b2744c0b77 Czech Republic (CZ)</p> <p>ed352558-77c4-4518-8f73-bc643b3f30e7 Poland (PL)</p> <p>9b95baa7-9d6a-4c87-b1a2-e693ddf60d04 Netherlands (NL)</p> <p>2745c03b-b342-4c16-baae-3fea733b0a5a Netherlands (NL)</p>

27dddce0-676d-464b-82f9-c5734e0a37e2 Estonia (EE)  
 74d22ada-9012-421a-8590-8c56a4fbadda Greece (GR)  
 87d4daa7-2618-4e33-8c94-9e175f7f1e44 Portugal (PT)  
 5e7b9acd-8049-430b-b5ff-6fb573ceb0a7 Bulgaria (BG)  
 af21d49d-f9ad-4cf4-ace6-cdb2b5aa35e9 Sweden (SE)  
 6ff4218c-dca4-4726-b424-da007c026354 France (FR)  
 cc207ae7-c10a-4a41-88c6-02d7dd46f977 Poland (PL)  
 749c0957-1647-4e3f-bb99-1ae1c7d430c4 Sweden (SE)  
 44fe9986-8844-4a40-8c1a-a3a98ffdda2b Germany (DE)  
 5b934c1d-9825-44a3-82e1-5b00b40ac18f Germany (DE)  
 fb34ba89-388c-4eac-9898-82a7676e4bb4 France (FR)  
 ad4fb7a8-ae09-49ad-8893-2f7f0b6d7c3a Netherlands (NL)  
 23b06215-b4f9-42c3-9b3b-095991a46bc2 Spain (ES)  
 4089c87c-2dbc-468b-a47a-9315d12a28ea Netherlands (NL)

**Environmental**

Ambient Air Temperature	Storage -15...+60 °C
RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	No declaration needed
SCIP	f83a26df-8beb-4c54-8294-808bd2c4e276 Switzerland (CH)
Simplified SCIP	0be49677-cc9e-4fc0-8911-f5e8389c541f Germany (DE) a4440343-c230-4a57-b9ba-9a8fa52e5c59 Poland (PL) 74e69599-e852-4d23-a06f-0aa85d2d9167 Norway (NO) 59cb3396-823b-47ab-b751-83fac10ee147 Finland (FI) 2a8ec393-df14-4c7a-a20d-43e5f434a50d Netherlands (NL) 436f430c-8f55-4869-a5ca-b26b90e0bbd1 Germany (DE) 8ad784ba-0575-4d1d-a283-146baf9c1224 Denmark (DK) cd38ab98-683c-4bba-83d4-5da51343320c Croatia (HR) 3437a7e2-88b6-4b36-89c0-d8b2744c0b77 Czech Republic (CZ) ed352558-77c4-4518-8f73-bc643b3f30e7 Poland (PL) 9b95baa7-9d6a-4c87-b1a2-e693ddf60d04 Netherlands (NL) 2745c03b-b342-4c16-baae-3fea733b0a5a Netherlands (NL) 27dddce0-676d-464b-82f9-c5734e0a37e2 Estonia (EE) 74d22ada-9012-421a-8590-8c56a4fbadda Greece (GR) 87d4daa7-2618-4e33-8c94-9e175f7f1e44 Portugal (PT) 5e7b9acd-8049-430b-b5ff-6fb573ceb0a7 Bulgaria (BG) af21d49d-f9ad-4cf4-ace6-cdb2b5aa35e9 Sweden (SE) 6ff4218c-dca4-4726-b424-da007c026354 France (FR) cc207ae7-c10a-4a41-88c6-02d7dd46f977 Poland (PL) 749c0957-1647-4e3f-bb99-1ae1c7d430c4 Sweden (SE) 44fe9986-8844-4a40-8c1a-a3a98ffdda2b Germany (DE) 5b934c1d-9825-44a3-82e1-5b00b40ac18f Germany (DE) fb34ba89-388c-4eac-9898-82a7676e4bb4 France (FR) ad4fb7a8-ae09-49ad-8893-2f7f0b6d7c3a Netherlands (NL) 23b06215-b4f9-42c3-9b3b-095991a46bc2 Spain (ES) 4089c87c-2dbc-468b-a47a-9315d12a28ea Netherlands (NL)

**Technical**

Input Voltage (U <sub>in</sub> )	230 V
Input Voltage Type	AC
Rated Frequency (f)	Primary 50 Hz Primary 60 Hz Secondary 50 Hz Secondary 60 Hz
Apparent Power Output	1500 V·A
Rated Output Power	900 W
Communication Interface	USB, RS-232
Number of Phases	Primary - 1 Secondary - 1
Number of Outputs	C13 Connection 6
Connection Type	IEC C14
Display Type	LCD
Options Provided	Auto shut down function
Battery Chemical Composition	Lead-Acid

Battery Type	Portable
Battery Weight	2.5 kg
Number of Batteries	2

## Dimensions

Product Net Width	146 mm
Product Net Height	205 mm
Product Net Depth / Length	395 mm
Product Net Weight	11.1 kg

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	236 mm
Package Level 1 Height	297 mm
Package Level 1 Depth / Length	496 mm
Package Level 1 Gross Weight	13.3 kg
Package Level 1 EAN	7640169262685

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044000
E-Number (Finland)	8408632
Country of Origin	China (CN)

## Certificates and Declarations

Declaration of Conformity - CCC	No certification needed
Declaration of Conformity - CE	4NWD004322

## Popular Downloads

Data Sheet, Technical Information	4NWD004444_ML
Instructions and Manuals	4NWD004444_ML
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658

## Classifications

ETIM 7	EC000382 - UPS
ETIM 8	EC000382 - UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000

---

eClass	V11.1 : 27040690
Object Classification Code	G

---

---

## Categories

---

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 LI IEC 230V

