

PRODUCT-DETAILS

UPS PowerValue 11LI Pro 2000 VA

UPS PowerValue 11LI Pro 2000 VA



General Information

Extended Product Type	UPS PowerValue 11LI Pro 2000 VA
Product ID	4NWP100179R0001
EAN	7640169262692
Catalog Description	UPS PowerValue 11LI Pro 2000 VA
Long Description	VI UPS PowerValue 11LI Pro 2000VA/1400W;230V;50/60Hz;pure sinewave;3 min

Circular Value

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD004620
RoHS Information	4NWD004322
SCIP	9ac61ad0-bce7-4de2-90ab-ae59d8741c58 Switzerland (CH)
Simplified SCIP	2fc58783-8e3b-4a59-995f-3879a910cf89 Germany (DE) 30ef323e-1f51-4c56-b41f-31a6eb23ae9b France (FR) f635ff1c-31cb-4b8b-a8d0-1ed0b1fdc15d Netherlands (NL) 6f9d26bd-428d-4070-9511-449f072469f1 Spain (ES) dd13423d-5b88-4702-8876-b7f3f031056a Netherlands (NL) 0c2b9eda-ad0a-42b6-9d4b-be6e3475d17c Portugal (PT) 03cc50bf-f9fe-4ead-8ac3-9240a96810fa Bulgaria (BG) 7452218c-d31a-49c1-930e-1b5eb1166519 Sweden (SE)

91d47e9f-b402-409f-9265-bf81b152b6a3 France (FR)
 ea7e4880-1cb9-4410-ae72-ec9477a1862f Poland (PL)
 52657760-8644-44f5-9716-ea46e38b3e7b Sweden (SE)
 c8ea79c1-efc7-4af6-bee8-c9b388caba31 Germany (DE)
 1732bf89-6bbb-4239-a1b2-c1f82dd18327 Germany (DE)
 438aa637-c8a8-44d6-ae34-6cb3daa18766 Poland (PL)
 436ade6c-b436-41d3-b670-a320e0967b15 Norway (NO)
 88f69724-41d7-49af-8394-90ca36955621 Finland (FI)
 649aa4d0-a639-4e86-afc3-218b7a4263da Netherlands (NL)
 3a691693-990e-41bb-b605-c5f564601da6 Germany (DE)
 ca6e3cb8-5d35-43d2-bdef-eee31d648820 Denmark (DK)
 784ca8b4-7926-4a9d-83b4-e64804f6d110 Croatia (HR)
 1cb37075-9aef-4462-b11c-99caaa82573e Czech Republic (CZ)
 c415c712-9a39-4239-955b-9b7b89aaa751 Poland (PL)
 72178fd6-7417-4881-a35f-a266b033de01 Netherlands (NL)
 d979c121-50a3-4e28-9e81-55da12eb7817 Netherlands (NL)
 12280d36-044a-4797-b89b-0c1b05bce20e Estonia (EE)
 00e54354-e8af-4378-9551-910dc36e4d3a Greece (GR)

Environmental

Ambient Air Temperature	Storage -15...+60 °C
RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	No declaration needed
SCIP	9ac61ad0-bce7-4de2-90ab-ae59d8741c58 Switzerland (CH)
Simplified SCIP	2fc58783-8e3b-4a59-995f-3879a910cf89 Germany (DE) 30ef323e-1f51-4c56-b41f-31a6eb23ae9b France (FR) f635ff1c-31cb-4b8b-a8d0-1ed0b1fdc15d Netherlands (NL) 6f9d26bd-428d-4070-9511-449f072469f1 Spain (ES) dd13423d-5b88-4702-8876-b7f3f031056a Netherlands (NL) 0c2b9eda-ad0a-42b6-9d4b-be6e3475d17c Portugal (PT) 03cc50bf-f9fe-4ead-8ac3-9240a96810fa Bulgaria (BG) 7452218c-d31a-49c1-930e-1b5eb1166519 Sweden (SE) 91d47e9f-b402-409f-9265-bf81b152b6a3 France (FR) ea7e4880-1cb9-4410-ae72-ec9477a1862f Poland (PL) 52657760-8644-44f5-9716-ea46e38b3e7b Sweden (SE) c8ea79c1-efc7-4af6-bee8-c9b388caba31 Germany (DE) 1732bf89-6bbb-4239-a1b2-c1f82dd18327 Germany (DE) 438aa637-c8a8-44d6-ae34-6cb3daa18766 Poland (PL) 436ade6c-b436-41d3-b670-a320e0967b15 Norway (NO) 88f69724-41d7-49af-8394-90ca36955621 Finland (FI) 649aa4d0-a639-4e86-afc3-218b7a4263da Netherlands (NL) 3a691693-990e-41bb-b605-c5f564601da6 Germany (DE) ca6e3cb8-5d35-43d2-bdef-eee31d648820 Denmark (DK) 784ca8b4-7926-4a9d-83b4-e64804f6d110 Croatia (HR) 1cb37075-9aef-4462-b11c-99caaa82573e Czech Republic (CZ) c415c712-9a39-4239-955b-9b7b89aaa751 Poland (PL) 72178fd6-7417-4881-a35f-a266b033de01 Netherlands (NL) d979c121-50a3-4e28-9e81-55da12eb7817 Netherlands (NL) 12280d36-044a-4797-b89b-0c1b05bce20e Estonia (EE) 00e54354-e8af-4378-9551-910dc36e4d3a Greece (GR)

Technical

Input Voltage (U _{in})	230 V
Input Voltage Type	AC
Rated Frequency (f)	Primary 50 Hz Primary 60 Hz Secondary 50 Hz Secondary 60 Hz
Apparent Power Output	2000 V·A

Rated Output Power	1200 W
Communication Interface	USB, RS-232
Number of Phases	Primary - 1 Secondary - 1
Number of Outputs	C13 Connection 6
Connection Type	IEC C14
Display Type	LCD
Options Provided	Auto shut down function
Battery Chemical Composition	Lead-Acid
Battery Type	Portable
Battery Weight	2.83 kg
Number of Batteries	2

Dimensions

Product Net Width	146 mm
Product Net Height	205 mm
Product Net Depth / Length	395 mm
Product Net Weight	11.9 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	236 mm
Package Level 1 Height	297 mm
Package Level 1 Depth / Length	496 mm
Package Level 1 Gross Weight	14.2 kg
Package Level 1 EAN	7640169262692

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044000
E-Number (Finland)	8408633
Country of Origin	China (CN)

Certificates and Declarations

Declaration of Conformity - CCC	No certification needed
Declaration of Conformity - CE	4NWD004322

Popular Downloads

Data Sheet, Technical Information	4NWD004444_ML
Instructions and Manuals	4NWD004444_ML
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658

Classifications

ETIM 7	EC000382 - UPS
ETIM 8	EC000382 - UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000
eClass	V11.1 : 27040690
Object Classification Code	G

Categories

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 LI IEC 230V

