HP Color Laser 150 Printer Series



Colour laser performance at an affordable price

Get productive print performance at an affordable price. Produce high-quality colour results and print and scan from your phone.^{2,7}

Dynamic security enabled printer. Only intended to be used with cartridges using an HP original chip. Cartridges using a non-HP chip may not work, and those that work today may not work in the future. Learn more at https://example.com/go/learnaboutsupplies





Legendary quality, surprisingly affordable price

- This surprisingly small laser delivers exceptional quality, page after page.
- Produce sharp text, bold blacks and crisp graphics.
- Rely on a high-performance laser printer at an affordable price.



Designed to fit your space

- Work efficiently with a small, compact printer – HP's smallest in-class.¹
- Get print speeds up to 18/4 ppm (A4).3



Easy mobile printing and scanning with HP Smart app⁷

- Get simple setup, and print and scan from your phone, with the HP Smart app.^{2,7}
- Easily print from a variety of smartphones and tablets.^{4,7}
- Easily share resources access and print with wireless networking.^{5,7}
- Connect your smartphone or tablet directly to your printer – and easily print without accessing a network.^{6,7}

¹ Smallest in-class footprint compared only to dimensions of majority of worldwide competing personal colour laser printers (defined as non-discontinued colour laser printers <\$200 USD) and colour laser MFPs <\$300 USD); HP internal research of printer manufacturers' published specifications as of Sept 4, 2018 and Keypoint Intelligence-Buyers Lab 2018 study commissioned by HP. Market share as reported by IDC CYQ2 2018 Hardcopy Peripherals Tracker. Footprint for HP Color Laser 150 printer series is 183 square inches, for HP Color Laser 170 MFP series is 228.8 square inches. For details, see keypointintelligence.com/HPColorLaser. ² Requires the HP Smart app download. For details on local printing requirements see hp.com/go/mobileprinting. ³ Excludes first et of test documents. For more information, see hp.com/go/printerclaims. Exact speed varies depending on the system configuration, software application, driver, and document complexity. ⁴ For details on local printing requirements see hp.com/go/mobile printing. ³ Wireless operations are compatible with 2.4 GHz and 5.0 GHz operations only. Learn more at hp.com/go/mobileprinting. Wi-Fi is a registered trademark of Wi-Fi Alliance®. ⁴ Mobile device needs to be connected to Wi-Fi Direct® signal of a Wi-Fi Directs printing. ¹ Signal of a Wi-Fi Directs is a registered trademark of Wi-Fi Alliance®. ⁴ Applicable to HP Color Laser ¹ Sonw Printer model only.

Product walkaround

HP Color Laser 150nw Printer shown



Series at a glance



¹ Requires the HP Smart app download. For details on local printing requirements, see https://np.com/go/printerclaims. ³ Wireless performance is dependent upon physical environment and distance from access point and may be limited during active VPN connections. ⁴ May require a firmware upgrade to be compatible, download at https://np.com/go/support ⁵ Not available in HP Color Laser 150a Printer.

HP Services

Downtime can have serious consequences, so HP provides support beyond the standard warranty. You benefit from reduced risk, maximized uptime, predictable service delivery and no unbudgeted repair costs. Choose from:

Optimized Care (optimum performance and stability): 4 hour Onsite Support. Maintenance Kit Replacement Service. Installation with Network Configuration Service

Standard Care (high level of uptime):

Next Business Day Onsite Support, Maintenance Kit Replacement Service, Installation with Network Configuration Service

Basic Care (minimum recommended support): Next Business Day Onsite Support

4 hour Onsite Support: Onsite support within four hours after a service call received within the coverage window

Next Business Day Onsite Support:

Onsite service the next business day after the service call is received

Maintenance Kit Replacement Service:

Onsite replacement of your printer's maintenance kit including parts, materials, and labor

Installation with Network Configuration Service: Assembly, network configuration, and basic administrator familiarization. For more information about HP Care Pack, HP Contractual, or HP Managed Print Services, visit hp.com/go/printservices











Top Features

This surprisingly small laser delivers exceptional quality, page after page.

Produce sharp text, bold blacks, and crisp colour graphics.

Rely on a high-performance laser printer at an affordable price.

Get simple setup, and print and scan from your phone, with the HP Smart app. 1,4

Easily print from a variety of smartphones and tablets.^{2,4}

Easily share resources – access and print with wireless and Ethernet networking.^{3,4}

Product

4ZB94A HP Color Laser 150a printer 4ZB95A HP Color Laser 150nw printer

Replacement Cartridges⁵

W2080A	HP 118A Black Original Laser Toner Cartridge (~1,000 pages) - China Only
W2081A	HP 118A Cyan Original Laser Toner Cartridge (~700 pages) - China Only
W2082A	HP 118A Yellow Original Laser Toner Cartridge (~700 pages) - China Only
W2083A	HP 118A Magenta Original Laser Toner Cartridge (~700 pages) - China Only
W2090A	HP 119A Black Original Laser Toner Cartridge (~700 pages) - APJ excluding China
W2091A	HP 119A Cyan Original Laser Toner Cartridge (~700 pages) - APJ excluding China
W2092A	HP 119A Yellow Original Laser Toner Cartridge (~700 pages) - APJ excluding China
W2093A	HP 119A Magenta Original Laser Toner Cartridge (~1,000 pages) - APJ excluding China
W1120A	HP 120A Original LaserJet Imaging Drum (~16,000 pages) - APJ excluding China
W1132A	HP 132A Original LaserJet Imaging Drum (~16,000 pages) - China Only
5KZ38A	HP Toner Collection Unit (7,000 pages)

HP Care Packs

UB4W7E HP 3-year Onsite Exchange Laser 15x MFP SVC

UB4X0E HP 3-year Next Business Day Exchange Laser 15x MFP SVC

UB4X3E HP 3-year Standard Exchange Laser 15x MFP SVC

Protect your investment with HP Care Pack. Let HP certified engineers resolve your technical issues. For more details on HP Care Pack, go to hp.com/go/cpc

Hewlett-Packard offices

Australia	613) 8833 5000	hp.com.au
China	(010) 6564 3888	hp.com.cn
Hong Kong	(852) 3077 2688	hp.com.hk
India	(80) 2612 9000	hp.com/in
Indonesia	(62-21) 5799 1088	hp.com/id
Malaysia	(603) 2332 3333	hp.com.my
New Zealand	(09) 918 9555	hp.co.nz
Philippines	(632) 888 5900	hp.com/ph
Singapore	(65) 6275 3888	hp.com.sg
Taiwan	(02) 8722 9000	hp.com.tw
Thailand	(662) 353 9500	hp.com/th
Vietnam	(848) 3823 4151	hp.com/vn

Recommended Papers⁴

CG964A HP Professional Laser Paper, Glossy, A4, 250 sheets, 120 gsm CG965A HP Professional Laser Paper, Glossy, A4, 150 sheets, 150 gsm HP Professional Laser Photo Paper, Glossy, A4, 100 sheets, 200 gsm CG966A Q6550A HP Professional Laser Photo Paper, Matte, A4, 100 sheets

Please visit hp.com/apac/paper for more details

HP Order-a-Cartridge⁶

Call HP's Order-a-Cartridge⁶ service and have them conveniently delivered to your doorstep.

800 820 0851/400 820 0851 China

India 1800 3003 3003

¹ Requires the HP Smart app download. For details on local printing requirements see hp.com/go/mobileprinting. 2 For details on local printing requirements see hp.com/go/mobile printing. 3 Wireless operations are compatible with 2.4 GHz and 5.0 GHz operations only. Learn more at hp.com/go/mobileprinting. Wi-Fi is a registered trademark of Wi-Fi Alliance®. Applicable to HP Color Laser 150nw Printer model only 5 Average color composite (C/M/Y) and black declared yields based on ISO/IEC 19798 and continuous printing. Actual yields vary considerably based on images printed and other factors. For details see hp.com/go/learnaboutsupplies. ⁶ Available in selected countries only.

Technical specifications

Model	HP Color Laser 150a Printer (4ZB94A)	HP Color Laser 150nw Printer (4ZB95A)	
Number of user	1-5	Users	
Functions	Print only	Print, Wireless	
Print			
Technology	Laser		
Duplex Print Options	Manual (driver support provided)		
Speed ¹	Black (normal, A4): Up to 18 ppm; Colour (normal, A4): Up to 4 ppm		
First page out ²	Black (A4, ready): As fast as 12.4 seconds; Black (A4, sleep): As fast as 13 seconds (15 min); Colour (A4, ready): As fast as 25.3 seconds; Colour (A4, sleep): As fast as 26 seconds (15 min)		
Resolution	Black (best): 600 x 600 dpi 4 bits; Black (normal): 600 x 600 dpi; Colour (best): 600 x 600 dpi 4 bits; Colour (normal): 600 x 600 dpi		
Cartridges number	4 (1 each black, cyan, magenta, yellow)		
Standard print languages	SPL		
Display	LE	D	
Control panel	3 Buttons (Resume, Cancel, Power): LED indicator lights (Attention, Power, C/M/Y/K Toner Gauge)	4 Buttons (Wireless, Resume, Cancel, Power): LED indicator lights (Attention Power, Wireless, C/M/Y/K Toner Gauge)	
Duty cycle (monthly, A4) ³	Up to 20,000 pages		
Recommended monthly page volume ⁴	100 to 500 pages		
Media			
Sizes (Supported)	Tray1: A4; A5; A6; B5 (JIS); Officio 216 x 340; 76 x 148.5 to 216 x 356 mm		
Weight (Supported)	60 to 220 g/m ²		
Types		l, Preprinted, Recycle, Labels, Bond, Glossy	
Paper handling	Input: 150-sheet input tray; Output: 50-sheet output bin		
Memory	Standard/Maximum: 64 MB		
Processor speed) MHz	
Operating system compatibility	Windows®: 7 (32/64 bit), 2008 Server R2, 8 (32/64 bit), 8.1 (32/64 bit), 10 (32/64 bit), 2012 Server, 2016 Server		
Minimum system requirements	PC: Windows 7 or newer, Intel® Pentium® IV 1 GHz 32-bit or 64-bit processor or higher, 1 GB RAM, 16 GB HDD		
Connectivity			
Connectivity (standard)	Hi-Speed USB 2.0 port	Hi-Speed USB 2.0 port, Fast Ethernet 10/100Base-TX network port, Wireless 802.11 b/g/n	
Wireless capability	Not available	Yes, built-in Wi-Fi 802.11b/g/n	
Mobile printing capability	Not available	Apple AirPrint™; Google Cloud Print™; Mobile Apps; Mopria™ Certified; Wi-Fi [®] Direct printing	
Supported network protocols	Not available	Via built-in networking solution: TCP/IP, IPv4, IPv6; print: TCP-IP port 9100 Direct Mode, LPD (raw queue support only), WSD; discovery: SLP, Bonjour, WS-Discovery; IP Config: IPv4 (BootP, DHCP, AutoIP, Manual), IPv6 (Stateless Link-Local and via Router, Stateful via DHCPv6); management: SNMPv1/v2/v3, HTTP	
Security management	Not available	Password-protected network embedded Web server; enable/disable Networl ports; SNMPv1 community password change; SNMPv2&V3 IPSec; Filtering: MAC, IPv4, IPv	
Environmental	1		
Acoustics	Acoustic power emissions (active, printing): 6.5B (A) (printing at 18 ppm with Mono mode); 6.1B (A) (printing at 4 ppm with Colour mode)		
Operating environment	Operating temperature range: 10 to 30° C; Recommended operating temperature: 15 to 27° C; Operating humidity range: 10 to 80% RH (non-condensing); Recommended operating humidity range: 20 to 70% RH (non-condensing); Storage temperature range: -20 to 40° C		
Energy savings feature technology	HP Auto-Off Technology; Power save		
Power specifications	Power supply type: Internal (Built-in) power supply; Power supply required: 110-volt input voltage: 110 to 127 VAC, 50/60Hz and 220-volt input voltage: 220 to 240 VAC, 50/60Hz; Power consumption: Active Printing: 282 W, Ready: 27 W, Sleep: 1.0 W, Manual off: 0.2 W, Auto off/Manual on: 0.2 W; Typical electricity consumption (TEC): 0.873 kWh/Week (BA), 0.988 kWh/Week (ES)		
Dimension (W x D x H) ⁷	382 x 309 x 211.5 mm		
Weight ⁸	10.04 kg		
Warranty	One-year limited hardware warranty; For	more info please visit us at <u>support.hp.com</u>	
What's in the box ⁹	HP Color Laser 150a Printer; Preinstalled introductory HP Laser Printer 0.7K pages Black, 0.5K pages Cyan, Yellow, Magenta print cartridges; Imaging drum, Toner collection unit; Installation guide, Getting Started guide, User's Guide, Support flyer, Warranty quide; No CD-ROM; Power cord; USB cable (AP)	HP Color Laser 150nw Printer; Preinstalled introductory HP Laser Printer 0.7K pages Black, 0.5K pages Cyan, Yellow, Magenta print cartridges; Imaging drum, Toner collection unit; Installation guide, Getting Started guide, User's Guide, Support flyer, Warranty guide; No CD-ROM; Power cord; USB cable (AP)	

Neasured using ISO/IEC 24734, excludes first set of test documents. For more information see https://www.hp.com/go/printerclaims. Exact speed varies depending on the system configuration, software application, driver, and document complexity. Duty cycle is defined as the maximum number of pages per month of imaged output. This value provides a comparison of product robustness in relation to other HP Laser Jet or HP Color Laser Jet devices, and enables appropriate deployment of printers and MFPs to satisfy the demands of connected individuals or groups. HP recommends that the number of printer pages per month be within the stated range for optimum device performance, based on factors including supplies replacement intervals and device life over an extended warranty period. Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Power consumption values typically based on measurement of 115V device. Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Power consumption values typically based on measurement of 115V device and 230V for Blue Angel. Dimensions vary as per configuration. Weight varies as per configuration, *Introductory cartridges included; yields 700 black pages. Replacement cartridge average declared yield 1,000 black, 700 colour based on ISO/IEC 19752. Actual yield varies considerably based on content of printed pages and other factors. For details see https://person.org/pc/learnaboutsupplies.

To learn more, visit hp.com

© 2020 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. To the extent allowed by law, HP shall not be liable for technical or editorial errors or omissions contained herein.

